



US1AUL THRU US1MUL


Single Phase 1.0AMP Surface Mount Ultra Fast Recovery Rectifier

Features

- Glass passivated device
- Ideal for surface mounted applications
- Low reverse leakage
- Metallurgically bonded construction
- High temperature soldering guaranteed:
260°C/10 seconds, 0.375"(9.5mm) lead length,
5 lbs. (2.3kg) tension
- Plastic material-UL flammability 94V-0

Mechanical Data

- Case: SOD-123FL, molded plastic
- Terminals: plated leads solderable per
MIL-STD-750, Method 2026
- Polarity: Color band denotes cathode end
- Mounting position: Any



Maximum Ratings and Electrical Characteristics

Rating at 25°C ambient temperature unless otherwise specified.

Single Phase, half wave, 60Hz, resistive or inductive load.

For capacitive load, derate current by 20%.

TYPE NUMBER	SYMBOL	US1AUL	US1BUL	US1DUL	US1GUL	US1JUL	US1KUL	US1MUL	UNITS
	Code	UAU	UBU	UDU	UGU	UJU	UKU	UMU	
Peak Repetitive Reverse Voltage	V_{RRM}								
Working Peak Reverse Voltage	V_{RWM}	50	100	200	400	600	800	1000	V
DC Blocking Voltage	V_{DC}								
RMS Reverse Voltage	V_{RMS}	35	70	140	280	420	560	700	V
Average Rectified Output Current @ $T_L = 90^\circ C$	$I_{F(AV)}$	1.0							A
Non-Repetitive Peak Forward Surge Current 8.3ms Single half sine-wave superimposed on rated load (JEDEC Method)	I_{FSM}	35							A
I^2t Rating for Fusing ($t < 8.3ms$)	I^2t	5.084							A ² s
Forward Voltage per element @ $I_F = 1.0A$	V_{FM}	1.0		1.4		1.7		V	
Peak Reverse Current @ $T_A = 25^\circ C$ At Rated DC Blocking Voltage @ $T_A = 125^\circ C$	I_R				5.0		100		μA
Maximum reverse recovery time (NOTE 1)	t_{rr}	50			75			ns	
Typical Junction Capacitance (Note 2)	C_J	8							pF
Typical thermal resistance	$R_{\theta JA}$	75							°C/W
Operating and Storage Temperature Range	T_J, T_{STG}	-55to+150							°C

Note:1.Measured with $I_F = 0.5A$, $I_R = 1A$, $I_{rr} = 0.25A$.

2.Measured at 1.0 MHz and Applied reverse Voltage of 4.0V D.C.



US1AUL THRU US1MUL

Single Phase 1.0AMP Surface Mount Ultra Fast Recovery Rectifier

Fig. 1 Typical Forward Current Derating Curve




Fig. 2 Typical Instantaneous Forward Characteristics




Fig. 3 Max Non-Repetitive Peak Fwd Surge Current




Fig.4 Typical Reverse Characteristics





Fig.5 Typical Capacitance





Important Notice and Disclaimer

- Reproducing and modifying information of the document is prohibited without permission from XINNUO
- XINNUO reserves the right to make changes to this document and its products and specifications
- XINNUO disclaims any and all liability arising out of the application or use of any product including damages incidentally and consequentially occurred.
- XINNUO does not assume any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.
- Applications shown on the here in document are examples of standard use and operation. Customers are responsible in comprehending the suitable use in particular applications.
XINNUO makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.
- The products shown here in are not designed and authorized for equipments requiring high level of reliability or relating to human life and for any applications concerning life-saving or life-sustaining, such as medical instruments, transportation equipment, aerospace machinery et cetera. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify XINNUO for any damages resulting from such improper use or sale.
- Since XINNUO uses lot number as the tracking base, please provide the lot number for tracking when complaining.