





- SPECIFICATIONS
- 1、Current Rating: 3A AC, DC
 - 2、Voltage Rating: 250V AC, DC
 - 3、Temperatuer Range: -25℃~ +85℃
 - 4、Contact Resistance: 30mΩ Max
 - 5、Insulation Resistance: 1000mΩ Min
 - 6、Withstanding Voltang: 800V AC/minute
 - 7、Material: Wafer Nylon UL94-V0(2)
PIN Brass Gold-plated

Circuit	Part NO.	Dimensions mm	
		A	B
2	HC-XHD-2P-G1	2.50	7.50
3	HC-XHD-3P-G1	5.00	10.00
4	HC-XHD-4P-G1	7.50	12.50
5	HC-XHD-5P-G1	10.00	15.00
6	HC-XHD-6P-G1	12.50	17.50
7	HC-XHD-7P-G1	15.00	20.00
8	HC-XHD-8P-G1	17.50	22.50
9	HC-XHD-9P-G1	20.00	25.00
10	HC-XHD-10P-G1	22.50	27.50
11	HC-XHD-11P-G1	25.00	30.00
12	HC-XHD-12P-G1	27.50	32.50

			GENERL TOLERANCE		制 图 DRAWING	 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM	TOL	审 核 CHECK				
			X. X	±0.30	批 准 APPROVAL	产品名称 TITLE	2.50 单排 直针 镀金	版本 REV.	A
1	初版发行		X. XX	±0.20	比 例 SCALE	产品料号 PART NO.	HC-XHD-NP-G1	单 位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日 期 MODIFY DATE	X. XXX	±0.10	投 影 Projection	材 料 MATERIAL		页 次 SHEET	1/1
			Angle	±3.0°					