







Not allowed to fall off





SECTION A-A

NOTES:

1. HOUSING MATERIAL:HIGH TEMPERATURE PLASTICS,UL94V-0.
2. CONTACT MATERIAL:COPPER ALLOY.
3. OPERATING TEMPERATURE RANGE:  $-40^{\circ}\text{C}\sim+105^{\circ}\text{C}$
4. STORAGE TEMPERATURE RANGE:  $-40^{\circ}\text{C}\sim+105^{\circ}\text{C}$
5. MINIMUM SOLDER STENCIL THICKNESS IS 0.12mm .
6. "▽"SIZE FOR CPK;
7. PRODUCT NUMBER MATRIX:

|                      |      |                 |                                    |
|----------------------|------|-----------------|------------------------------------|
|                      |      | APC5-24AX-X-001 |                                    |
| Power supply seat    |      | WTB             | Stream code                        |
| 2.20 pitch           |      |                 |                                    |
| T/H, R/A, Double Row |      |                 | NULL:Low temperature thermoplastic |
| T/H, R/A, Double Row |      |                 | F:High temperature thermoplastic   |
| Contact Plating:     |      |                 | H:Halogen free                     |
|                      |      |                 | T:Tray                             |
|                      |      |                 | K:REEL                             |
| Definition           | Code |                 |                                    |
| ◎Tin plated:         | A    |                 |                                    |



ShenZhen ShenTai weiXiang Electronics Co., Ltd.

TOLERANCE UNLESS OTHERWISE SPECIFIED

|        |       |        |     |
|--------|-------|--------|-----|
| X. X   | ±0.30 | X. °   | ±3° |
| X. XX  | ±0.20 | X. X°  | ±2° |
| X. XXX | ±0.10 | X. XX° |     |

SCALE 1:1

UNIT mm

SIZE A4



ORIGINAL DRAWN: ZW

CHECK: Xie. Yong

APPROVE: Ady zhou

DATE 2018.01.12

DATE 2018.01.12

DATE 2018.01.12

DWG. NO. 600-0000-0218

PARTS NO. (INTENDED USE)

APC5-24AK-F-001

TITLE


CUSTOMER DRAWING

REV.


1

SHEET


2/3




RECOMMENDED PCB LAYOUT (TOP SIDE)  
TOLERANCE  $\pm 0.05$



RECOMMENDED PCB LAYOUT (BOTTOM SIDE)  
TOLERANCE  $\pm 0.05$



STEEL MESH (TOP SIDE) T=0.12mm



STEEL MESH (BOTTOM SIDE) T=0.12mm



ShenZhen ShenTai weiXiang Electronics Co., Ltd.

TOLERANCE UNLESS OTHERWISE SPECIFIED

|        |            |        |               |
|--------|------------|--------|---------------|
| X. X   | $\pm 0.30$ | X. °   | $\pm 3^\circ$ |
| X. XX  | $\pm 0.20$ | X. X°  | $\pm 2^\circ$ |
| X. XXX | $\pm 0.10$ | X. XX° |               |

SCALE 1:1

UNIT mm

SIZE A4



ORIGINAL DRAWN:  
ZW

CHECK:  
Xie. Yong

APPROVE:  
Ady zhou

DATE 2018.01.12

DATE 2018.01.12

DATE 2018.01.12

DWG. NO. 600-0000-0218

PARTS NO. (INTENDED USE)

APC5-24AK-F-001

TITLE  
CUSTOMER DRAWING

REV.  
1  
SHEET  
3/3