




1





2





4




B



C



D



E


G-Switch USB-C Specification:

- 1.Current rated: 5A on vbus/1.25A on vconn/0.25A on other
Voltage rating: 24V AC
- 2.Withstanding voltage: 100V AC/minute
- 3.Contact resistance: 40mΩ Max
- 4.Insulation resistance: 100MΩ Min
- 5.Operating temperature: -40°C ~ +85°C
- 6.Mating force: 5N~20N
- 7.Unmating force: 8N~20N
- 8.Durability cycle:10,000 cycles

A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12
GND			VBUS	CC1	D+	D-	SBU1	VBUS			GND
First			First	Second	Second	Second	Second	First			First

B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1
GND			VBUS	SBU2	D-	D+	CC2	VBUS			GND
First			First	Second	Second	Second	Second	First			First

RECOMMENDED PCB LAYOUT
TOLERANCE:±0.05



RoHS
Compliant
EU RoHS Standards



SCALE: 1:1
UNIT: mm
SIZE: A4

Unless otherwise
General Tolerance:
X. ±0.50
X.x ±0.30
X.xx ±0.10
X.xxx ±0.05
X° ±2°

Title: Vertical Type-c 16P Female
SMT H=13.7mm

Molde Code: GT-USB-7082G

DRAWN	CHECKED	APPROVED	DATE
Xia	Chen	Chen	2023.02.01



REV: A0 SHEET: 1/1

5

NO.	PARTS	MATERIAL	REMARKS
1	SHELL	STAINLESS STEEL304	Ni PLATED
2	MID PLATE	STAINLESS STEEL304	Ni PLATED
3	HOUSING	HIGH TEMPERATURE PLASTIC	LCP/PA9T BLACK UL 94 V-0
4	TERMINALS	C7025/C1814	Au1u" PLATING ON CONTACT AREA Au1u" PLATING ON SOLDERED AREA