







NOTES 备注:

1. MATERIAL 材料:

1.1 HOUSING 胶壳: THERMOPLASTIC, HIGH TEMP, UL94V-0, COLOR: SEE PART NO.

1.2 LATCH 锁存器: THERMOPLASTIC, HIGH TEMP, UL94V-0, COLOR: SEE PART NO.

1.3 CONTACTS 端子: COPPER ALLOY.

1.4 DUMMY CARD 卡: THERMOPLASTIC, HIGH TEMP, UL94 V-0, COLOR: BLACK.

2. FINISH 电镀:


CONTACT 端子:

SELECTIVE GOLD PLATING ON THE CONTACT AREA.

100μ" MIN. MATTE-TIN PLATING ON THE SOLDER TAILS,

50μ" MIN. NICKEL UNDERPLATING OVERALL.

PCB Thickness "DIM. K"		DIMENSIONS				
		POSITION	A±0.20	B ^{+0.20} _{-0.08}	D ±0.25	E ±0.55
0	2.08	36	6	7.65	25	36.2
1	2.30	64	20	21.65	39	50.2
2	1.80	98	37	38.65	56	67.2
4	1.57	164	70	71.65	89	100.2



ΔX
ΔX
ΔX
MARK

日期

DESCRIPTION

REVISIONS

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn

DATE

REVISED


APPROVED

ANGULAR
L ≤ 4 ±5°
4 < L ≤ 16 ±0.2
16 < L ≤ 63 ±0.3
L > 63 ±0.4
UNSPECIFIED TOLERANCES

XKLB

XKB INDUSTRIAL PRECISION CO., LIMITED

DSND		SCALE: N/A	MODEL TYPE:
DWN		VIEW:	PART NO.: X1622WS-XX-9TV15
CHKD		UNIT: mm/in	DWG NO.: X-X1622WS-XX-9TV15
APPD		SIZE: A4	
		WEIGHT	SHEET
		1/1	REVISION A0



X1622 W S - XX - 9T V15

- ① ② ③ ④ ⑤ ⑥
- ① Series Nunber
② Terminal form: W-Wafer
③ Welding Board Angle : Straddle
④ No. of Pins: 36~164 Pin
⑤ Plastic material: PA9T /PA46 UL94V-0
⑥ Contact Plating: V15-Gold 15u"
V30-Gold 30u"

POS.	DIM. A	DIM. H	"M"
36	6	8.15	B17
64	20	22.15	B31
98	37	39.15	B48
164	70	72.15	B81

RECOMMENDED PCB LAYOUT
TOLERANCE: ±0.05

广东星坤科技股份有限公司

日期
文件工程章



文件工程章

DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
REVISIONS				
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn				

DSND		SCALE: N/A	MODEL TYPE:
DWN		VIEW:	PART NO.: X1622WS-XX-9TV15
CHKD		UNIT: mm/in	DWG NO.: X-X1622WS-XX-9TV15
APPD		SIZE: A4	WEIGHT SHEET REVISION
			1/1 A0

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED



WITH Dummy Card

DIMENSIONS	
POSITION	DIM. F
36	20.4
64	34.4
98	51.4
164	84.4

广东星坤科技股份有限公司

ΔX		日
ΔX		期
ΔX		
MARK	DESCRIPTION	

文件工程章

REVISIONS					UNSPECIFIED TOLERANCES	
DATE	REVISED	APPROVED	DESCRIPTION		ANGULAR	±5°
					L≤ 4	±0.2
					4<L≤ 16	±0.3
					16<L≤ 63	±0.4
					L> 63	±0.5

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn



XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE:
DWN		VIEW:	PART NO.: X1622WS-XX-9TV15
CHKD		UNIT: mm/in	DWG NO.: X-X1622WS-XX-9TV15
APPD		SIZE: A4	
WEIGHT	SHEET 1/1	REVISIOI	A0