





3D View

- NOTES:
- MATERIAL
 - 1-1: SUS-304 THICKNE=0.10MM
 - SPECIFICATIONS
 - 2-1: RATED CURRENT: 1.0A
 - 2-2: VOLTAGE RATING: 1.5V
 - 2-3: CONTACT RESISTANCE: 80mΩ/MAX
 - 2-4: WELDING THRUST: ≥3KG
 - 2-5: OPERATING TEMPERATURE: -40°C~+85°C
 - DURABILITY: 1500 CYCLES
 - SALT SPRAY TIME: 24H
 - ELECTROPLATE: THE NICKEL-PLATED SUBSTRATE IS 50u" MIN
 - REQUIREMENTS
 - 6-1: TERMINAL TO EAT FULL TIN, NOT PEELING, WELDING OBVIOUS COLOR AND OTHER ADVERSE
 - 6-2: ROHS, REACH, HF HALOGER ADVERSE OF DOMESTIC AND INTERNATIONAL ENVIRONMENTAL REQUIREMENTS





RECOMMENDED PCB LAYOUT

TOLERANCE: ±0.05MM
(FOR REFERENCE ONLY)



METAL MASK T=0.08

TOLERANCE: ±0.05MM
(FOR REFERENCE ONLY)



(For Reference Only)
Stated At Compression

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: 天线弹片 L3.50*W1.50*H2.50
DECIMALS:	ANGLES:		PAR ASP-D2501-B01
X. ±0.30	X. ° ±0.20	DWN	
.X ±0.20	.X ° ±0.10	CHKD	
.XX ±0.15	.XX ° ±0.5	APVD	
CUSTOMER COPY		SCALE N:A	UNIT:MM
		SIZE:A4	SHEET:1F1
			REV:A

ROHS Compliant




MAPX	MODIFICATION	DATE	DRAW	APPROVE

ASP-D2501-B01

Customer To Use Direction

Pull Out Direction

(出料方向)



MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd						
UNLESS OTHERWISE SPECIFIED TOLERANCES								
DECIMALS:	ANGLES:					PAR		
X. ±0.30	X. ° ±0.20					DWN		
.X ±0.20	.X ° ±0.10					CHKD		
.XX ±0.15	.XX ° ±0.5					APVD		
CUSTOMER COPY		SCALE N:A	UNIT:MM	⊕				
		SIZE:A4	SHEET:1F1	REV:A				