

2RXXXS-8×6 Series


Features

- Size: 8.2mm*6mm
- Stable breakdown voltage.
- High insulation resistance.
- Low capacitance ($\leq 1\text{pF}$)
- High holdover voltage
- Storage and operational temperature: $-40^{\circ}\text{C} \sim +90^{\circ}\text{C}$

Applications

- Transient Voltage Surge Suppression(TVSS)
- Cable Telephone Product
- Modems/Cable Modems
- Broadband/CATV/Coaxial Protectors
- Communication Lines
- Power Supplies

Specification Status:Draft (mm)



Electrical Characteristics (TA = 25 °C unless otherwise noted)


Part Number	DC Breakdown Voltage	Tolerance	Impulse Spark-over Voltage	Impulse Discharge Current 10hits(5hits each polarity)	AC Discharge Current 5 hits	Insulation Resistance*	Capacitance
	100V/s	of Vs	1kv/ μs	8/20 μs	50Hz	G Ω	1MHz
2R075S-8×6	75V	±20%	≤600V	10KA	10A	≥10	≤1pF
2R090S-8×6	90V	±20%	≤600V	10KA	10A	≥10	≤1pF
2R150S-8×6	150V	±20%	≤700V	10KA	10A	≥10	≤1pF
2R200S-8×6	200V	±20%	≤700V	10KA	10A	≥10	≤1pF
2R230S-8×6	230V	±20%	≤700V	10KA	10A	≥10	≤1pF
2R300S-8×6	300V	±20%	≤900V	10KA	10A	≥10	≤1pF
2R350S-8×6	350V	±20%	≤1000V	10KA	10A	≥10	≤1pF
2R400S-8×6	400V	±20%	≤1000V	10KA	10A	≥10	≤1pF
2R470S-8×6	470V	±20%	≤1200V	10KA	10A	≥10	≤1pF
2R600S-8×6	600V	±20%	≤1400V	10KA	10A	≥10	≤1pF

1)At delivery AQL 0.65 leave II Military Standard 105 E.


2)In ionized mode

3)Test according to ITU-T Rec.k.12

Marking





Reflow soldering curve



$T_{E \max} = 180^\circ\text{C}$ $t_{E \max} = 60\text{s (at } T_{E \max})}$
 $T_B \max = 220^\circ\text{C}$
 $T_P \max = 250^\circ\text{C}$ $t_{P \max} = 300\text{s}$ $t_{p \max} = 220\text{s (typical)}$

Package



- NOTE:
1. Material: POLYSTYRENE;
 2. All dimensions in millimeters;
 3. 10 sprocket hole pitch cumulative tolerance $\pm 0.2\text{mm}$.
 4. Part conforms to IEC 60286-3.



DIMENSION IN MM							
W	16.00±0.30	P	12.00±0.10	AO	8.60±0.10	BO	6.40±0.10
S		P0	4.00±0.10				
E	1.75±0.10	P2	2.00±0.10				
F	7.50±0.10	D0	$\phi 1.50 \pm \begin{smallmatrix} 0.10 \\ 0 \end{smallmatrix}$	KO	8.50±0.10		
T	0.50±0.05	D1				COLOR : B	