



PCB Layout(Pattern side)



① ————— ②

Circuit Diagram



NO.1			
PART NO	H	PART NO	H
A	4.3	O	11
B	4.5	P	11.5
C	5	Q	12
D	5.5	R	12.5
E	6	S	13
F	6.5	T	13.5
G	7	U	14
H	7.5	V	15
I	8	W	16
J	8.5	X	17
K	9	Y	18
L	9.5	Z	19
M	10	1	15.5
N	10.5		

NO.2	
PART NO	vigor
1	90±30
2	130±30
3	180±30
4	250±30
5	350±50

NO.4~NO.5	
PART NO	NOTE
01~99	SERIAL NUMBER

⑤	Terminal	—	2	Brass(0.30t)	Plating silver	_____
④	Contact	—	1	F.Ag/SUS	Plating silver	_____
③	Base	—	1	Nylon	Black	_____
②	Cover	—	1	Brass	Plating Sn	_____
①	Keystoke	—	1	Nylon	Black	_____
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS		DATE	TITLE:	TACT SWITCHS	
DRAWN	LIUCAN	2020.12.16		PART NO.	K2-1102DE-□□SW-□□
CHECKED					
APPROVALS					

TOLERANCES ARE	30~以上	±0.30	ANGLE UNIT: mm	SCALE: 1:1	PROJ:
	10~30	±0.20			
	5~10	±0.15			
	~ 5	±0.10			
DRAWING NO.					SHEET 1 OF 1

—	A	—	NEW	—	
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.