

# S1D015120A

## Silicon Carbide Schottky Diode

$V_{RRM}$	=	1200 V
$I_F (T_C=135^\circ\text{C})$	=	22 A
$Q_C$	=	82 nC

### Feature

- 1.2kv schottky Rectifier
- Zero Reverse Recovery Current / Zero forward recovery
- High-Frequency Operation
- Temperature-Independent Switching
- Low forward voltage
- Positive Temperature Coefficient on  $V_F$

### Benefits

- Replace Bipolar with Unipolar Rectifiers
- Essentially No Switching Losses
- High Efficiency
- Reduction of Heat Sink Requirements
- Parallel Devices Without Thermal Runaway

### Applications

- Switch Mode Power Supplies
- Power Factor Correction
- Motor Drives
- AC/DC converters

### Package



TO-220-2L



Part Number	Package	Marking
S1D015120A	TO-220-2L	S1D015120A

### Maximum Ratings ( $T_c = 25^\circ\text{C}$ unless otherwise specified )

Symbol	Parameter	Value	Unit	Test Conditions	Note
$V_{RRM}$	Repetitive Peak Reverse Voltage	1200	V		
$V_{RSM}$	Surge Peak Reverse Voltage	1300	V		
$V_R$	DC Peak Reverse Voltage	1200	V		
$I_F$	Continuous Forward Current	15	A	$T_c = 158^\circ\text{C}$	Fig.7
$I_{FSM}$	Non-Repetitive Peak Forward Surge Current	140	A	$T_c = 25^\circ\text{C}$ , $t_p = 10$ ms, Half Sine Pulse	
$P_{tot}$	Power Dissipation	187 81	W	$T_c = 25^\circ\text{C}$ $T_c = 110^\circ\text{C}$	
dV/dt	Diode dV/dt ruggedness	200	V/ns	$V_R = 0\sim 960\text{V}$	
$\int i^2 dt$	$\int i^2 dt$	162	A <sup>2</sup> S	$T_c = 25^\circ\text{C}$ , $t_p = 10$ ms	
$T_{stg}, T_J$	Operating Junction Range	-55 to +175	$^\circ\text{C}$		

## Electrical Characteristics

Symbol	Parameter	Typ.	Max.	Unit	Test Conditions	Note
$V_F$	Forward Voltage	1.4 1.9	1.8 3	V	$I_F = 15A, T_J = 25^\circ C$ $I_F = 15A, T_J = 175^\circ C$	Fig.1
$I_R$	Reverse Current	1 7	100 200	$\mu A$	$V_R = 1200V, T_J = 25^\circ C$ $V_R = 1200V, T_J = 175^\circ C$	Fig.2
$Q_c$	Total Capacitive Charge	82		nC	$V_R = 800V, I_F = 15A$ $di/dt = 200A/\mu s, T_J = 25^\circ C$	Fig.4
C	Total Capacitance	1500 74 52		pF	$V_R = 0V, T_J = 25^\circ C, f = 1MHz$ $V_R = 400V, T_J = 25^\circ C, f = 1MHz$ $V_R = 800V, T_J = 25^\circ C, f = 1MHz$	Fig.3
$E_c$	Capacitance Stored Energy	43		$\mu J$	$V_R = 800V$	Fig.5

## Thermal Characteristics

symbol	parameter	Typ	Unit	Note
$R_{\theta JC}$	Thermal Resistance from Junction to Case	0.8	$^\circ C/W$	Fig. 7

## Typical Performance




Figure 1: Forward Characteristics




Figure 2: Reverse Characteristics




Figure 3: Capacitance vs. Reverse Voltage




Figure 4: Recovery Charge vs. Reverse Voltage




Figure 5: Typical Capacitance Stored Energy




Figure 6: Power Derating





Figure 7: Transient Thermal Impedance

## Package Dimensions

Package TO-220-2L



## **Attention**

---

### **1. Rohs compliance**

The levels of RoHS restricted materials in this product are below the maximum concentration values (also referred to as the threshold limits) permitted for such substances, or are used in an exempted application, in accordance with EU Directive 2011/65/ EC (RoHS2), as implemented January 2, 2013.

### **2. REACH compliance**

REACH substances of high concern (SVHCs) information is available for this product. Since the European Chemical Agency (ECHA) has published notice of their intent to frequently revise the SVHC listing for the foreseeable future, please contact a Sichain representative to insure you get the most up-to-date REACH SVHC Declaration. REACH banned substance information (REACH Article 67) is also available upon request.

3. With respect to information regarding the application of the product, Sichain hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

4. Any information given in this documents subject to customer's compliance with its obligations and any applicable legal requirements, norms and standards concerning any use of the product of Sichain in any customer's applications.

5. Specifications of any and all products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment.

6. Due to technical requirements products may contain dangerous substances. For information on the types in question please contact Sichain office.

7. Except as otherwise explicitly approved by Sichain in a written document signed by authorized representatives of Sichain, Sichain' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.

8. For use of our products in applications requiring a high degree of reliability (as exemplified below), please contact and consult with a Sichain representatives, for example but not limited to: transportation equipment, primary communication equipment, traffic lights, fire/crime prevention, safety equipment, medical systems, and power transmission systems.