

# **Product Specification**

## XBLW IRFR024NT

N-Channel Enhancement Mode MOSFETs











#### **Description**


The IRFR024NT uses advanced trench technology to provide excellent RDS(ON), low gate charge and operation with gate voltages as low as 4.5V. This evice is suitable for use as a Battery protection or in other Switching application.

#### **General Features**

- ➤ VDS = 60V ID =30 A
- $\triangleright$  RDS(ON) < 26m $\Omega$  @ VGS=10V

#### **Application**

- Battery protection
- Load switch
- Uninterruptible power supply



#### N-Channel MOSFET

### **Package Marking and Ordering Information**

Product Model	Package Type	Marking	Packing	Packing Qty
XBLW IRFR024NT	TO-252-2L	IRFR024NT	Tape	2500Pcs/Reel

#### **Absolute Maximum Ratings (TC=25°Cunless otherwise noted)**

Symbol	Parameter	Rating	Units
Vps	Drain-Source Voltage	60	V
Vgs	Gate-Source Voltage	±20	V
I <sub>D</sub> @T <sub>C</sub> =25°C	Continuous Drain Current, V <sub>GS</sub> @ 10V <sup>1</sup>	30	А
I <sub>D</sub> @T <sub>C</sub> =100°C	Continuous Drain Current, V <sub>GS</sub> @ 10V <sup>1</sup>	15	А
I <sub>D</sub> @T <sub>A</sub> =25°C	Continuous Drain Current, V <sub>GS</sub> @ 10V <sup>1</sup>	5.6	А
I <sub>D</sub> @T <sub>A</sub> =70°C	Continuous Drain Current, V <sub>GS</sub> @ 10V <sup>1</sup>	4.5	А
Ірм	Pulsed Drain Current <sup>2</sup>	46	А
EAS	Single Pulse Avalanche Energy <sup>3</sup>	25.5	mJ
las	Avalanche Current	22.6	Α
P <sub>D</sub> @T <sub>C</sub> =25°C	Total Power Dissipation <sup>4</sup>	34.7	W
P <sub>D</sub> @T <sub>A</sub> =25°C	Total Power Dissipation <sup>4</sup>	2	W
Тѕтс	Storage Temperature Range	-55 to 150	°C
TJ	Operating Junction Temperature Range	-55 to 150	°C
R <sub>0</sub> JA	Thermal Resistance Junction-Ambient <sup>1</sup>	62	°C/W
R <sub>0</sub> Jc	Thermal Resistance Junction-Case <sup>1</sup>	3.6	°C/W



#### **Electrical Characteristics (TJ=25 °C, unless otherwise noted)**


Symbol	Parameter	Conditions	Min.	Тур.	Max.	Unit
BVDSS	Drain-Source Breakdown Voltage	V <sub>GS</sub> =0V , I <sub>D</sub> =250uA	60			V
△BVbss/△TJ	BV <sub>DSS</sub> Temperature Coefficient	Reference to 25°C , I <sub>D</sub> =1mA		0.063		V/°C
_		V <sub>GS</sub> =10V , I <sub>D</sub> =15A		22	26	
RDS(ON)	Static Drain-Source On-Resistance <sup>2</sup>	V <sub>GS</sub> =4.5V , I <sub>D</sub> =10A		30	38	mΩ
V <sub>G</sub> S(th)	Gate Threshold Voltage	V V 1 050 A	1.2		2.5	V
$\triangle V_{GS(th)}$	V <sub>GS(th)</sub> Temperature Coefficient	$-V_{GS}=V_{DS}$ , $I_D=250uA$		-5.24		mV/°C
		V <sub>DS</sub> =48V , V <sub>GS</sub> =0V , T <sub>J</sub> =25°C			1	
IDSS	Drain-Source Leakage Current	V <sub>DS</sub> =48V , V <sub>GS</sub> =0V , T <sub>J</sub> =55°C			5	uA
Igss	Gate-Source Leakage Current	V <sub>GS</sub> =±20V , V <sub>DS</sub> =0V			±100	nA
gfs	Forward Transconductance	V <sub>DS</sub> =5V , I <sub>D</sub> =15A		17		S
Rg	Gate Resistance	V <sub>DS</sub> =0V , V <sub>GS</sub> =0V , f=1MHz		3.2		Ω
Qg	Total Gate Charge (4.5V)			12.6		
Qgs	Gate-Source Charge	V <sub>DS</sub> =48V , V <sub>GS</sub> =4.5V , I <sub>D</sub> =12A		3.2		nC
Q <sub>gd</sub>	Gate-Drain Charge			6.3		
Td(on)	Turn-On Delay Time			8		
Tr	Rise Time	V <sub>DD</sub> =30V , V <sub>GS</sub> =10V ,		14.2		
Td(off)	Turn-Off Delay Time	R <sub>G</sub> =3.3 ,		24.4		ns
T <sub>f</sub>	Fall Time			4.6		
Ciss	Input Capacitance			1378		
Coss	Output Capacitance	── V <sub>DS</sub> =15V , V <sub>GS</sub> =0V , f=1MHz		86		pF
Crss	Reverse Transfer Capacitance			64		
Is	Continuous Source Current <sup>1,5</sup>				23	Α
Ism	Pulsed Source Current <sup>2,5</sup>	─V <sub>G</sub> =V <sub>D</sub> =0V , Force Current			46	Α
Vsp	Diode Forward Voltage <sup>2</sup>	V <sub>GS</sub> =0V , I <sub>S</sub> =1A , T <sub>J</sub> =25°C			1.2	V
<u> </u>			l .	l		

#### Note:

- 1.The data tested by surface mounted on a 1 inch2 FR-4 board with 2OZ copper.
- 2.The data tested by pulsed , pulse width  $\leqq$  300us , duty cycle  $\leqq$  2%
- 3.The EAS data shows Max. rating . The test condition is VDD=25V,VGS=10V,L=0.1mH,IAS=22.6A
- 4.The power dissipation is limited by 150°C junction temperature
- $5. The \ data \ is \ theoretically \ the \ same \ as \ ID \ and \ IDM$  , in real applications , should be limited by total power dissipation.



## **Typical Characteristics**



**Fig.1 Typical Output Characteristics** 




Fig.3 Forward Characteristics of Reverse




Fig.5 Normalized V<sub>GS(th)</sub> v.s T<sub>J</sub>




Fig.2 On-Resistance v.s Gate-Source




Fig.4 Gate-Charge Characteristics





Fig.6 Normalized  $R_{\text{DSON}}$  v.s  $T_{\text{J}}$ 






Fig.7 Capacitance

Fig.8 Safe Operating Area




Fig.9 Normalized Maximum Transient Thermal Impedance




Fig.10 Switching Time Waveform





Fig.11 Unclamped Inductive Waveform



## **Package Information**

#### TO252-2L



Comple of	Dimensions In Millimeters		Dimensions In Inches		
Symbol	Min.	Max.	Min.	Max.	
Α	2.200	2.400	0.087	0.094	
A1	0.000	0.127	0.000	0.005	
b	0.660	0.860	0.026	0.034	
С	0.460	0.580	0.018	0.023	
D	6.500	6.700	0.256	0.264	
D1	5.100	5.460	0.201	0.215	
D2	0.483 TYP.		0.190 TYP.		
E	6.000	6.200	0.236	0.244	
e	2.186	2.386	0.086	0.094	
L	9.800	10.400	0.386	0.409	
L1	2.900 TYP.		0.114 TYP.		
L2	1.400	1.700	0.055	0.067	
L3	1.60	0 TYP.	0.06	0.063 TYP.	
L4	0.600	1.000	0.024	0.039	
Ф	1.100	1.300	0.043	0.051	
θ	0.	8.	0。	8。	
h	0.000	0.300	0.000	0.012	
V	5.35	0 TYP.	0.211 TYP.		



#### Statement:

- XBLW reserves the right to modify the product manual without prior notice! Before placing an order, customers need to confirm whether the obtained information is the latest version and verify the completeness of the relevant information.
- Any semi-guide product is subject to failure or malfunction under specified conditions. It is the buyer's responsibility to comply with safety standards when using XBLW products for system design and whole machine manufacturing. And take the appropriate safety measures to avoid the potential in the risk of loss of personal injury or loss of property situation!
- XBLW products have not been licensed for life support, military, and aerospace applications, and therefore XBLW is not responsible for any consequences arising from the use of this product in these areas.
- If any or all XBLW products (including technical data, services) described or contained in this document are subject to any applicable local export control laws and regulations, they may not be exported without an export license from the relevant authorities in accordance with such laws.
- The specifications of any and all XBLW products described or contained in this document specify the performance, characteristics, and functionality of said products in their standalone state, but do not guarantee the performance, characteristics, and functionality of said products installed in Customer's products or equipment. In order to verify symptoms and conditions that cannot be evaluated in a standalone device, the Customer should ultimately evaluate and test the device installed in the Customer's product device.
- XBLW documentation is only allowed to be copied without any alteration of the content and with the relevant authorization. XBLW assumes no responsibility or liability for altered documents.
- XBLW is committed to becoming the preferred semiconductor brand for customers, and XBLW will strive to provide customers with better performance and better quality products.