


## SOD-323 Plastic-Encapsulate Diodes

ZENER DIODE

### FEATURE

- Planar Die Construction
- General Purpose, Medium Current
- Ideally Suited for Automated Assembly Processes
- Available in Lead Free Version



### Maximum Ratings(Ta=25°C unless otherwise specified)

| Characteristic                                   | Symbol                            | Value      | Unit |
|--------------------------------------------------|-----------------------------------|------------|------|
| Forward Voltage (Note 2) @ I <sub>F</sub> = 10mA | V <sub>F</sub>                    | 0.9        | V    |
| Power Dissipation(Note 1)                        | P <sub>d</sub>                    | 200        | mW   |
| Thermal Resistance from Junction to Ambient      | R <sub>θJA</sub>                  | 625        | /W   |
| Operation Junction and Storage Temperature Range | T <sub>J</sub> , T <sub>stg</sub> | -55 ~ +150 |      |

## ELECTRICAL CHARACTERISTICS







$T_a = 25^\circ\text{C}$  unless otherwise specified

| Type Number | Type Code | Zener Voltage Range (Note 2) |        |        |          | Maximum Zener Impedance (Note 3) |                   |          | Maximum Reverse Current |       | Typical Temperature Coefficient @ $I_{ZTC}$<br>mV/°C |      | Test Current $I_{ZTC}$ |
|-------------|-----------|------------------------------|--------|--------|----------|----------------------------------|-------------------|----------|-------------------------|-------|------------------------------------------------------|------|------------------------|
|             |           |                              |        |        |          |                                  |                   |          |                         |       |                                                      |      |                        |
|             |           | $V_Z @ I_{ZT}$               |        |        | $I_{ZT}$ | $Z_{ZT} @ I_{ZT}$                | $Z_{ZK} @ I_{ZK}$ | $I_{ZK}$ | $I_R$                   | $V_R$ | Min                                                  | Max  |                        |
|             |           | Nom(V)                       | Min(V) | Max(V) | mA       | $\Omega$                         |                   | mA       | $\mu\text{A}$           | V     |                                                      |      | mA                     |
| BZT52B2V4S  | 2WX       | 2.4                          | 2.35   | 2.45   | 5        | 100                              | 600               | 1.0      | 50                      | 1.0   | -3.5                                                 | 0    | 5                      |
| BZT52B2V7S  | 2W1       | 2.7                          | 2.65   | 2.75   | 5        | 100                              | 600               | 1.0      | 20                      | 1.0   | -3.5                                                 | 0    | 5                      |
| BZT52B3V0S  | 2W2       | 3.0                          | 2.94   | 3.06   | 5        | 95                               | 600               | 1.0      | 10                      | 1.0   | -3.5                                                 | 0    | 5                      |
| BZT52B3V3S  | 2W3       | 3.3                          | 3.23   | 3.37   | 5        | 95                               | 600               | 1.0      | 5                       | 1.0   | -3.5                                                 | 0    | 5                      |
| BZT52B3V6S  | 2W4       | 3.6                          | 3.53   | 3.67   | 5        | 90                               | 600               | 1.0      | 5                       | 1.0   | -3.5                                                 | 0    | 5                      |
| BZT52B3V9S  | 2W5       | 3.9                          | 3.82   | 3.98   | 5        | 90                               | 600               | 1.0      | 3                       | 1.0   | -3.5                                                 | 0    | 5                      |
| BZT52B4V3S  | 2W6       | 4.3                          | 4.21   | 4.39   | 5        | 90                               | 600               | 1.0      | 3                       | 1.0   | -3.5                                                 | 0    | 5                      |
| BZT52B4V7S  | 2W7       | 4.7                          | 4.61   | 4.79   | 5        | 80                               | 500               | 1.0      | 3                       | 2.0   | -3.5                                                 | 0.2  | 5                      |
| BZT52B5V1S  | 2W8       | 5.1                          | 5.00   | 5.20   | 5        | 60                               | 480               | 1.0      | 2                       | 2.0   | -2.7                                                 | 1.2  | 5                      |
| BZT52B5V6S  | 2W9       | 5.6                          | 5.49   | 5.71   | 5        | 40                               | 400               | 1.0      | 1                       | 2.0   | -2.0                                                 | 2.5  | 5                      |
| BZT52B6V2S  | 2WA       | 6.2                          | 6.08   | 6.32   | 5        | 10                               | 150               | 1.0      | 3                       | 4.0   | 0.4                                                  | 3.7  | 5                      |
| BZT52B6V8S  | 2WB       | 6.8                          | 6.66   | 6.94   | 5        | 15                               | 80                | 1.0      | 2                       | 4.0   | 1.2                                                  | 4.5  | 5                      |
| BZT52B7V5S  | 2WC       | 7.5                          | 7.35   | 7.65   | 5        | 15                               | 80                | 1.0      | 1                       | 5.0   | 2.5                                                  | 5.3  | 5                      |
| BZT52B8V2S  | 2WD       | 8.2                          | 8.04   | 8.36   | 5        | 15                               | 80                | 1.0      | 0.7                     | 5.0   | 3.2                                                  | 6.2  | 5                      |
| BZT52B9V1S  | 2WE       | 9.1                          | 8.92   | 9.28   | 5        | 15                               | 100               | 1.0      | 0.5                     | 6.0   | 3.8                                                  | 7.0  | 5                      |
| BZT52B10S   | 2WF       | 10                           | 9.80   | 10.20  | 5        | 20                               | 150               | 1.0      | 0.2                     | 7.0   | 4.5                                                  | 8.0  | 5                      |
| BZT52B11S   | 2WG       | 11                           | 10.78  | 11.22  | 5        | 20                               | 150               | 1.0      | 0.1                     | 8.0   | 5.4                                                  | 9.0  | 5                      |
| BZT52B12S   | 2WH       | 12                           | 11.76  | 12.24  | 5        | 25                               | 150               | 1.0      | 0.1                     | 8.0   | 6.0                                                  | 10.0 | 5                      |
| BZT52B13S   | 2WI       | 13                           | 12.74  | 13.26  | 5        | 30                               | 170               | 1.0      | 0.1                     | 8.0   | 7.0                                                  | 11.0 | 5                      |
| BZT52B15S   | 2WJ       | 15                           | 14.70  | 15.30  | 5        | 30                               | 200               | 1.0      | 0.1                     | 10.5  | 9.2                                                  | 13.0 | 5                      |
| BZT52B16S   | 2WK       | 16                           | 15.68  | 16.32  | 5        | 40                               | 200               | 1.0      | 0.1                     | 11.2  | 10.4                                                 | 14.0 | 5                      |
| BZT52B18S   | 2WL       | 18                           | 17.64  | 18.36  | 5        | 45                               | 225               | 1.0      | 0.1                     | 12.6  | 12.4                                                 | 16.0 | 5                      |
| BZT52B20S   | 2WM       | 20                           | 19.60  | 20.40  | 5        | 55                               | 225               | 1.0      | 0.1                     | 14.0  | 14.4                                                 | 18.0 | 5                      |
| BZT52B22S   | 2WN       | 22                           | 21.56  | 22.44  | 5        | 55                               | 250               | 1.0      | 0.1                     | 15.4  | 16.4                                                 | 20.0 | 5                      |
| BZT52B24S   | 2WO       | 24                           | 23.52  | 24.48  | 5        | 70                               | 250               | 1.0      | 0.1                     | 16.8  | 18.4                                                 | 22.0 | 5                      |
| BZT52B27S   | 2WP       | 27                           | 26.46  | 27.54  | 2        | 80                               | 300               | 0.5      | 0.1                     | 18.9  | 21.4                                                 | 25.3 | 2                      |
| BZT52B30S   | 2WQ       | 30                           | 29.40  | 30.60  | 2        | 80                               | 300               | 0.5      | 0.1                     | 21.0  | 24.4                                                 | 29.4 | 2                      |
| BZT52B33S   | 2WR       | 33                           | 32.34  | 33.66  | 2        | 80                               | 325               | 0.5      | 0.1                     | 23.1  | 27.4                                                 | 33.4 | 2                      |
| BZT52B36S   | 2WS       | 36                           | 35.28  | 36.72  | 2        | 90                               | 350               | 0.5      | 0.1                     | 25.2  | 30.4                                                 | 37.4 | 2                      |
| BZT52B39S   | 2WT       | 39                           | 38.22  | 39.78  | 2        | 130                              | 350               | 0.5      | 0.1                     | 27.3  | 33.4                                                 | 41.2 | 2                      |

- Notes: 1. Device mounted on ceramic PCB: 7.6mm x 9.4mm x 0.87mm with pad areas 25mm<sup>2</sup>.  
2. Short duration test pulse used to minimize self-heating effect.  
3.  $f = 1\text{kHz}$ .


## Typical Characteristics

Notes: Our company currently provide 5.1 V - 20 V products only



## SOD-323 Tape and Reel

### SOD-323 Embossed Carrier Tape



#### Packaging Description:

SOD-323 parts are shipped in tape. The carrier tape is made from a dissipative (carbon filled) polycarbonate resin. The cover tape is a multilayer film (Heat Activated Adhesive in nature) primarily composed of polyester film, adhesive layer, sealant, and anti-static sprayed agent. These reeled parts in standard option are shipped with 3,000 units per 7" or 17.8cm diameter reel. The reels are clear in color and is made of polystyrene plastic (anti-static coated).

| Dimensions are in millimeter |      |     |      |       |      |      |      |      |      |      |
|------------------------------|------|-----|------|-------|------|------|------|------|------|------|
| Pkg type                     | A    | B   | C    | d     | E    | F    | P0   | P    | P1   | W    |
| SOD-323                      | 1.48 | 3.3 | 1.25 | Ø1.50 | 1.75 | 3.50 | 4.00 | 4.00 | 2.00 | 8.00 |

### SOD-323 Tape Leader and Trailer

