

60V N-Channel Enhancement Mode MOSFET

MAIN CHARACTERISTICS

I_D	160A
V_{DSS}	60V
R_{DS(on)}-typ(@V_{GS}=10V)	<3mΩ(Type:2.8mΩ)

Features


Adopt advanced trench technology to provide excellent Battery protection or in other Switching application.

Applications

- ◆ Battery protection
- ◆ Load switch
- ◆ Uninterruptible power supply
- ◆ **YFW-SGT technology**

Mechanical Data

- ◆ Case: Molded plastic
- ◆ Mounting Position: Any
- ◆ Molded Plastic: UL Flammability Classification Rating 94V-0
- ◆ Lead free in compliance with EU RoHS 2011/65/EU directive
- ◆ Solder bath temperature 275℃ maximum, 10s per JESD 22-B106



Product Specification Classification

Part Number	Package	Marking	Pack
YFWG160N06NF	PDFN5*6-8L	YFW G160N06NF XXXXX	5000PCS/Tape

Maximum Ratings at Tc=25°C unless otherwise specified

Characteristics	Symbol	Value	Unit
Drain-Source Voltage	V_{DS}	60	V
Gate-Source Voltage	V_{GS}	± 20	V
Continue Drain Current	I_D	160	A
Pulsed Drain Current (Note1)	I_{DM}	240	A
Power Dissipation	P_D	210	W
Single Pulse Avalanche Energy (Note1)	E_{AS}	650	mJ
Operating Temperature Range	T_J	150	°C
Storage Temperature Range	T_{STG}	-55 to +150	°C
Thermal Resistance, Junction to Case	$R_{\theta JC}$	0.59	°C/W
Thermal Resistance, Junction to Ambient	$R_{\theta JA}$	50	°C/W

Note1:Pulse test: 300 μ s pulse width, 2 % duty cycle

Electrical Characteristics at Tc=25°C unless otherwise specified







Characteristics	Test Condition	Symbol	Min	Typ	Max	Unit
Drain-Source Breakdown Voltage	$V_{GS} = 0\text{ V}, I_D = 250\text{ }\mu\text{A}$	BV_{DSS}	60	-	-	V
Drain-Source Leakage Current	$V_{DS} = 60\text{ V}, V_{GS} = 0\text{ V}$	I_{DSS}	-	-	1	μA
Gate Leakage Current	$V_{GS} = \pm 20\text{ V}, V_{DS} = 0\text{ V}$	I_{GSS}	-	-	± 100	nA
Gate-Source Threshold Voltage	$V_{DS} = V_{GS}, I_D = 250\text{ }\mu\text{A}$	$V_{GS(th)}$	2	-	4	V
Drain-Source On-State Resistance	$V_{GS} = 10\text{ V}, I_D = 20\text{ A}$	$R_{DS(on)}$	-	2.8	3	m Ω
Transconductance	$V_{DS}=5\text{ V}, I_D=20\text{ A}$	gfs		130		S
Input Capacitance	$V_{DS}=25\text{ V}, V_{GS}=0\text{ V}, f=1\text{ MHz}$	C_{iss}	-	4200	-	pF
Output Capacitance		C_{oss}	-	1080	-	pF
Reverse Transfer Capacitance		C_{rss}	-	41	-	pF
Turn-on Delay Time(Note2)	$V_{DD}=30\text{ V}, V_{GS}=10\text{ V}, RG=3\Omega, I_D=100\text{ A}$	$t_{d(ON)}$	-	13.5	-	ns
Rise Time(Note2)		t_r	-	95.5	-	ns
Turn-Off Delay Time(Note2)		$t_{d(OFF)}$	-	40	-	ns
Fall Time(Note2)		t_f	-	110	-	ns
Total Gate Charge(Note2)	$V_{DS}=30\text{ V}, V_{GS}=10\text{ V}, I_D=20\text{ A}$	Q_G	-	42	-	nC
Gate to Source Charge(Note2)		Q_{GS}	-	10	-	nC
Gate to Drain Charge(Note2)		Q_{GD}	-	12	-	nC

Source-Drain Diode Characteristics at Ta=25°C unless otherwise specified







Characteristics	Test Condition	Symbol	Min.	Typ.	Max.	Unit
Maximun Body-Diode Continuous Current		I_S	-	-	160	A
Drain-Source Diode Forward Voltage	$V_{GS}=0\text{ V}, I_S=20\text{ A}, T_J=25\text{ }^\circ\text{C}$	V_{SD}	-	-	1.2	V
Reverse Recovery Time(Note2)	$T_J = 25\text{ }^\circ\text{C}, I_F=60\text{ A}$ $di / dt = 100\text{ A}/\mu\text{s}$	t_{rr}	-	35	-	ns
Reverse Recovery Charge(Note2)		Q_{rr}	-	30	-	nC

Note2:Pulse test: 300 μ s pulse width, 2 % duty cycle

RATINGS AND CHARACTERISTIC CURVES



RATINGS AND CHARACTERISTIC CURVES



Package Outline Dimensions Millimeters

PDFN5*6-8L

Technical drawing of the YFWG160N06NF package showing three views: top, bottom, and side.

- Top View:** Shows a square package with a central circular feature. Dimensions include L (total width), L1 (width of the central feature), L2 (width of the central feature), and R (radius of the central feature).
- Bottom View:** Shows the underside of the package with mounting tabs. Dimensions include B (width of the mounting tabs), E (height of the mounting tabs), and R (radius of the central feature).
- Side View:** Shows the profile of the package. Dimensions include A (height of the package), C (width of the package), C1 (width of the package at the base), and C2 (width of the package at the top).

Dim.	Min.	Max.
A	4.8	5.2
B	0.25	0.35
C	1	1.2
C1	Typ0.254	
C2	Typ0.254	
E	Typ1.27	
L	6	6.3
L1	5.7	6
L2	Max0.2	
R	Typ13°	
All Dimensions in millimeter		