








SCHEMATIC



Recommended P.C.B Layout

技术要求

1、ELECTRICAL CHARACTERISTICS(电气性能):

1.1 Rating(额定值): DC12V 0.5A

1.2 Travel(行程): 0.25±0.1mm

1.3 Contact Resistance(接触电阻): 100mΩ Max

1.4 Life(寿命): 50,000 Cycles MIN(大于50,000次)

2、ELECTRICAL temperature rang(使用温度范围): -16° C~+60° C

PAPT NO	TC1104N-X-X	
Operating Force	160 : 160gf ; 260 : 260gf	
Height	43 : 4.3mm	75 : 7.5mm
	45 : 4.5mm	80 : 8.0mm
	50 : 5.0mm	85 : 8.5mm
	55 : 5.5mm	90 : 9.0mm
	60 : 6.0mm	95 : 9.5mm
	65 : 6.5mm	100 : 10.0mm
	70 : 7.0mm	10.5mm...17mm

		new		2015/5/3		A		瀚源	
ECN BO.		DESCRIPTION.		DATE.		REV.			
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER				SCALT: 1/2	SCALE: 3:1	
Mikey	Tom	Jerry	PART NAME	TC1104N-X-X		UNLESS OTHERWISE SPECIFIED,TOLERANCE:	X.	±0.25	
			MODEL NAME	TC1104N-X-X	X.x		±0.20		
					X.xx		±0.15		
			3RD ANGLE PROJ	HanElectricity Co.,LTD			ANGULAIR	±3	
								FILE.NO.	