




	A	B	C	D	E	F	G				
1	性能参数			13. Electrical life: 500000 cycles 电气寿命: 500000 cycles							
	1. Heating current: Ui: AC250V, Ith: 5A 发热电流: Ui: AC250V, Ith: 5A			14. mechanical: 500000cycles 机械寿命: 500000cycles							
	2. Rated current:3A/DC36V 额定电流:3A/DC36V			15. Operation method:Self-locking type 操作方式: 自锁式							
	3. Power-frequency withstand voltage:2000V1min 工频耐压:2000V1min			16. NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N							
	4. Insulation resistance:≥1000MΩ 绝缘电阻 :≥1000MΩ			17. LED lamp power consumption: 20m以下 LED灯功耗: 20m以下							
2	5. Contact resistance:≤50mΩ 接触电阻 :≤50mΩ			18. LED lamp lifespan: 40000h LED寿命: 40000h							
	6. Pressing stroke:3.00mm ± 0.10 按压行程:3.00mm ± 0.10			19. LED color: Red LED颜色: 红色							
	7. Contact stroke:1.50mm±0.10 接触行程 :1.50mm±0.10										
	8. Nut assembly torque:5-14N 螺帽装配力矩:5-14N										
	9. Protection level:IP67 防护等级:IP67										
	10. Explosion prevention level: IK10 防暴等级: IK10										
3	11. Working environment temperature: -20 ℃~+55 ℃ 工作环境温度: -20 ℃~+55 ℃										
	12. Compression torque: ≤ 6N 按压扭力: ≤6N										
	连接形式										
	1. Welding temperature of wire: 320 ± 20 ℃ 线材焊接温度: 320±20℃ Wire welding duration: less than 3 seconds 线材焊接时长: 时长3秒以下										
4	2. Can be used with dedicated connectors: 可配专用接插件使用:										
	2.1 1NO1NC Switch function wire: green (C) blue wire (NO) yellow wire (NC) 1NO1NC 开关功能线材: 绿色(C) 蓝线 (NO) 黄线 (NC)										
	2.2 2NO2NC switch function wire: green black wire (C), blue black wire (NO), yellow white wire (NC) 2NO2NC开关功能线材: 绿黑线(C)、蓝黑线 (NO)、黄白线 (NC)										
	2.3 LED functional wire: red wire positive pole, black wire negative pole, LED without distinction between positive and negative poles LED功能线材: 红线正极, 黑线负极, LED不分正负极										
5	A4			 台普 ROC PU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
	A3				X.XX ± 0.10		DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91924P124RA
	A2				X.X ± 0.15		DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
	A1				X ± 0.25		ROC PU TECHNOLOGY CO.,LTD				
	REV	DATE	REVISION DESCRIPTION		ISSUE	ANGULAR					
	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basis of manufacture or sale of apparatus without permission										
	A	B	C	D	E	F	G				

	A	B	C	D	E	F	G																																																															
1	材质参数 <table border="1"> <tr> <td>10</td><td>luminous zone 发光区</td><td>PC 塑料</td><td>1</td><td></td></tr> <tr> <td>9</td><td>LEDpin LED脚</td><td>Brass 黄铜</td><td>1</td><td>Silvering 镀银</td></tr> <tr> <td>8</td><td>Base 底座</td><td>PA46</td><td>1</td><td></td></tr> <tr> <td>7</td><td>Pin 引脚</td><td>Brass 黄铜</td><td>1</td><td>gold-plating 镀金</td></tr> <tr> <td>6</td><td>Contact material 接触材质</td><td>silver alloy 银合金</td><td>1</td><td>Silvering 镀银</td></tr> <tr> <td>5</td><td>LED Base LED基座</td><td>PC 塑料</td><td>1</td><td></td></tr> <tr> <td>4</td><td>Arm nut 固定螺帽</td><td>Brass 黄铜</td><td>1</td><td>nickeling 镀镍</td></tr> <tr> <td>3</td><td>Oring O型圈</td><td>Silica gel 硅胶</td><td>1</td><td></td></tr> <tr> <td>2</td><td>Housing 外壳</td><td>Aluminum alloy 铝合金</td><td>1</td><td>Oxidized/Black 氧化/黑色</td></tr> <tr> <td>1</td><td>Key 按键</td><td>Aluminum alloy 铝合金</td><td>1</td><td>Oxidized/Black 氧化/黑色</td></tr> <tr> <td>NO 序号</td><td>Part name 部件名</td><td>Material 材料</td><td>QTY 数量</td><td>Remark 备注</td></tr> </table>						10	luminous zone 发光区	PC 塑料	1		9	LEDpin LED脚	Brass 黄铜	1	Silvering 镀银	8	Base 底座	PA46	1		7	Pin 引脚	Brass 黄铜	1	gold-plating 镀金	6	Contact material 接触材质	silver alloy 银合金	1	Silvering 镀银	5	LED Base LED基座	PC 塑料	1		4	Arm nut 固定螺帽	Brass 黄铜	1	nickeling 镀镍	3	Oring O型圈	Silica gel 硅胶	1		2	Housing 外壳	Aluminum alloy 铝合金	1	Oxidized/Black 氧化/黑色	1	Key 按键	Aluminum alloy 铝合金	1	Oxidized/Black 氧化/黑色	NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注	1								
10	luminous zone 发光区	PC 塑料	1																																																																			
9	LEDpin LED脚	Brass 黄铜	1	Silvering 镀银																																																																		
8	Base 底座	PA46	1																																																																			
7	Pin 引脚	Brass 黄铜	1	gold-plating 镀金																																																																		
6	Contact material 接触材质	silver alloy 银合金	1	Silvering 镀银																																																																		
5	LED Base LED基座	PC 塑料	1																																																																			
4	Arm nut 固定螺帽	Brass 黄铜	1	nickeling 镀镍																																																																		
3	Oring O型圈	Silica gel 硅胶	1																																																																			
2	Housing 外壳	Aluminum alloy 铝合金	1	Oxidized/Black 氧化/黑色																																																																		
1	Key 按键	Aluminum alloy 铝合金	1	Oxidized/Black 氧化/黑色																																																																		
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注																																																																		
2							2																																																															
3							3																																																															
4							4																																																															
5	<table border="1"> <tr> <td>A4</td><td></td><td></td><td></td><td rowspan="5">  台普 ROCPCU </td><td colspan="2">COMMON TOLERANCE</td><td>UNIT</td><td>MM</td><td>PROJECTED</td><td></td><td>PRODUCT NAME:</td></tr> <tr> <td>A3</td><td></td><td></td><td></td><td>DRAWN BY</td><td>FUYUAN</td><td>CHECKED BY</td><td>COCO</td><td colspan="3">MODEL NO: TP91924P124RA</td></tr> <tr> <td>A2</td><td></td><td></td><td></td><td>DATE</td><td>2019</td><td>APPROVAL B</td><td>ALEN</td><td colspan="3">Https: www.rocpcu.tw</td></tr> <tr> <td>A1</td><td></td><td></td><td></td><td colspan="7" rowspan="2"> ROCPCU TECHNOLOGY CO.,LTD </td></tr> <tr> <td>REV</td><td>DATE</td><td>REVISION</td><td>DESCRIPTION</td><td>ISSUE</td></tr> <tr> <td></td><td></td><td></td><td></td><td></td><td>ANGULAR</td><td>—</td><td colspan="6">Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission</td></tr> </table>						A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:	A3				DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91924P124RA			A2				DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw			A1				ROCPCU TECHNOLOGY CO.,LTD							REV	DATE	REVISION	DESCRIPTION	ISSUE						ANGULAR	—	Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission						5
A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED			PRODUCT NAME:																																																										
A3					DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91924P124RA																																																													
A2					DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw																																																													
A1					ROCPCU TECHNOLOGY CO.,LTD																																																																	
REV	DATE	REVISION	DESCRIPTION									ISSUE																																																										
					ANGULAR	—	Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission																																																															
	A	B	C	D	E	F	G																																																															