


# RoHS

REV	ECN NO.	DESCRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	更换图框			2023.11.25



### SPECIFICATIONS

1. Current rating: 1A AC, DC
2. Temperature range: -40°C ~ +105°C
3. Insulation resistance: 100MΩ Min.
4. Withstanding voltage: 250V AC/ minute.
5. Contact resistance: 20mΩ Max.



### Material:

Insulator: LCP UL 94V-0  
 Contact: Brass  
 Solder Tab: Brass  
 Plating: Matte Tin or gold plated over Nickel  
 Circuits: 2~08  
 Mate with: XFCN P1250 series Housing  
 Ordering Code:


M1250RS-XX-LP

材质: LP=LCP

Pin位数 2=02P  
 8=08P



No. of PIN/ROW	Dimension	
	A	B
2	1.25	7.20
3	2.50	8.45
4	3.75	9.70
5	5.00	10.95
6	6.25	12.20
7	7.50	13.45
8	8.75	14.70



PCB LAYOUT

X.±0.50	X.°±
.XX±0.25	.X°±
.XX±0.15	.XX°±
.XXX±0.10	.XXX°±
UNITS:	mm

PART NO: M1250RS-XX-LP		<b>XFCN</b> 兴飞连接器	
TITLE: 1.25mm Crimp Style Connectors		0769-82001899	
		www.xfconn.com	
		DWG NO: /	
APPD	Chen ZhiQiang	VIEW	
CHKD	Liu Wei	SCALE	SHEET
DRAW	Chen HongJiang	SCALE	REV
DATE	2024.05.24	NONE	1:1 A1

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN