

承認書

SPECIFICATION FOR APPROVAL




客户名稱
CUSTOMER

客户料号
CUS. P/N

尺寸
DIMENSION **CT2-12x6x7**

編號
SERIAL NO. **NO.1026132177**

日期
DATE **2024年5月6日**

出圖 DRAWING		
發行 ISSUE	復核 CHECKED	核準 APPROVAL
		
DATE: 2024/5/6		

承認 CUSTOMER APPROVAL



东莞市灿峰电子有限公司

DONG GUAN CITY CAN FENG ELETRONICS CO., LTD

网址: www.canfengele.com E-mail: canfengdianzi@163.com


联系方式

王小姐: 13556646144

洪先生: 13809826886






承認書

SPECIFICATION FOR APPROVAL

規格 ITEM	CT2-12x6x7		編號 SERIAL NO.	NO.1026132177	
1. 形狀尺寸 (單位mm) ; SHAPE & DIMENSION(unit/mm); 			A	12.00 ± 0.5	mm
			B	6.00 ± 0.5	mm
			C	7.00 ± 0.5	mm
			D		
			E		
			F		
			G		
			2. 電器性能檢測項目 ELECTTRONICAL REQUIREMENTS;		
<input type="checkbox"/> L		TEST FREQ		測試儀器 TESTING INSTRUMENTS	
<input type="checkbox"/> Q		TEST FREQ	KHZ MHZ	1. Q-METER: <input type="checkbox"/> HP-4342A <input type="checkbox"/> MQ-172	
<input checked="" type="checkbox"/> Z	Z1=20 Ω MIN 25MHZ	KHZ	Z3=	KHZ MHZ	2. LCR-METER: <input type="checkbox"/> TH2826
	Z2=60 Ω MIN 100MHZ	KHZ	Z4=	KHZ MHZ	3. IMPEDANCE ANALYZER: <input checked="" type="checkbox"/> HP-4191A <input type="checkbox"/> Agilent 16092A <input type="checkbox"/> E4991A
溫度 TEMP	25±5℃	濕度 HUMIDITY	60±8%		4. L-METER: <input type="checkbox"/> TH-2775B
繞線: WINDING	Z: Φ 0.5*100L(mm)*0.5TS			5. DIGITAL MINI-OHM METER: VP2941A	
3. 外觀 THE LIMIT OF BREAKACE:					
項目 Item			標準值 Standard Value		
一處缺陷的面积 Area of a breakage			≤1mm ²		
总缺陷面积 ALL area of the breakage			≤2mm ²		
缺陷深度 The depth of the breakge			≤0.4mm		
毛刺长度 The length of burr			≤0.2mm		
4. 包裝 PACKAGING: 內包裝采用泡塑盒, 外包裝采用紙箱, 每箱產品外面都蓋上标签 (包括品名、數量、批號、檢驗員)。 Inner packing gdopts foam plastics box, outer packing adopts carton and each carton should have a qualified label outside(include the variey, quantity, batch number and inspector).					

檢 測 數 據

INSPECTION DATA

規 格 ITEM	CT2-12x6x7					編 號 SERIAL NO.	NO.1026132177					
1. 形壯尺寸(单位/毫米): SHAPE & DIMENSION(unit/mm): = 							<input type="checkbox"/> L					
							<input type="checkbox"/> Q					KHZ MHZ
							<input checked="" type="checkbox"/> Z	Z1=20 Ω MIN	KHZ	Z1=	KHZ	
								25MHZ		Z2=60 Ω MIN	KHZ	Z4=
								100MHZ				
							溫 度 TEMP	25±5°C	濕 度 HUMIDITY	60±8%		
繞 線: WINDING	Z: Φ 0.5*100L(mm)*0.5TS											
項 目 ITEM	電 氣 性 能 ELECTRONIC CHARACTERISTICS						尺 寸 DIMENSION(unit:mm)					
	Q	L(μH)	Z1(Ω)	Z2(Ω)	Z3(Ω)	Z4(Ω)	A	B	C	D	E	F
			20	60			12	6	7			
+			/	/			0.5	0.5	0.5			
-			0	0			0.5	0.5	0.5			
1			30.6	87.0			11.99	6.02	7.01			
2			30.8	82.1			11.95	6.01	7.02			
3			31.1	92.2			12.02	6.02	7.01			
4			31.3	89.3			11.98	6.08	7.04			
5			37.3	84.6			11.95	6.00	6.99			
6			40.7	95.2			12.05	6.08	6.98			
7			41.6	88.2			12.02	6.01	7.04			
8			37.0	87.2			12.05	6.03	7.04			
9			38.8	89.1			12.02	6.04	6.99			
10			29.6	96.6			12.01	6.07	7.00			
X			34.9	89.2			12.00	6.04	7.01			
Y/N			Y	Y			Y	Y	Y			
2. 測試儀器 TESTING INSTRUMENTS E4991A+16194A 							檢 測 INSPECTION	復 核 CHECK	確 認 APPROVAL			
												


阻抗 - 頻率曲綫




IMPEDANCE V.S.FREQUENCY (Z-Y)

規格 ITEM	CT2-12x6x7	編號 SERIAL NO.	NO.1026132177
------------	------------	------------------	---------------

材质特性：
MATERIAL CHARACTERISTICS

材料 牌号 Material	初始磁 导率 Initial Permeability	比损耗因子 Relative Loss Factor	比温度系数 Relative Temperature Coefficient	饱和磁通密度 Saturation Magnetic Flux Density	剩磁 Reman- ence	矫顽力 Coercivi- ty	居里温度 Curie Tempera- ture	电阻率 Electric Resistiv- ity	使用范围 Applied Frequenc- y Range	密度 Densit- y
Unit symbol	μ_i $\pm 20\%$	$\tan \delta / \mu_i$ $\times 10^{-6}$	$\alpha \mu_i \gamma$ $\times 10^{-6}$	Bs (MT)	Br (MT)	HC (A/m)	Tc (°C)	ρ ($\Omega \cdot m$)	F Mhz	d g/cm ³
F2	650	20(0.1MHz)	2-5	260(1600A/m)	150	35	>140	>10 ⁵	0.1-1.5	4.6



测试条件； TESTING CONDITION;	檢 測 INSPECTION	復 核 CHECK	确 認 APPROVAL
1. 测试仪器： E4991A+16194A Testing Equipment:			
2. 测试频率区间： 1MHZ-500MHZ Testing Frequency Range:			
3. 测试绕组： $\Phi 0.5 \times 100L(mm) \times 0.5TS$ Testing Coil Specification:			