

# MSKSEMI 美森科

SEMICONDUCTOR



ESD



TVS



TSS



MOV



GDT



PLED

## **MS13N50P/F**

---

### **Product specification**

## Description

The MS13N50P/F can be used in various power switching circuit for system miniaturization and higher efficiency. The package form is TO-220/ TO-220F, which accords with the RoHS standard






## General Features

- $V_{DS}=500V, I_D=13A$
- $R_{DS(ON)} < 0.48\Omega @ V_{GS}=10V$

## Application

- Power switch circuit of adaptor and charger

## Reference News

| PACKAGE OUTLINE  |  | P-Channel MOSFET   | Marking  |  |
|--|--|--|--|--|
|  |  |  |  |  |
| TO-220   | TO-220F  |  | MS13N50P   | MS13N50F   |

Note : \*\*\*\*Representative production cycle

## Absolute Maximum Ratings@T<sub>J</sub>=25°C (unless otherwise specified)

| Symbol             | Parameter  | 13N50P     | 13N50F | Unit |
|--------------------|--|------------|--------|------|
| $V_{DSS}$          | Drain-to-Source Voltage  | 500        |        | V    |
| $V_{GSS}$          | Gate-to-Source Voltage   | ±30        |        |      |
| $I_D$              | Continuous Drain Current   | 13         |        | A    |
| $I_{DM}$           | Pulsed Drain Current at $V_{GS}=10V$   | 52         |        |      |
| $E_{AS}$           | Single Pulse Avalanche Energy  | 900        |        | mJ   |
| $P_D$              | Power Dissipation  | 195        | 48     | W    |
|                    | Derating Factor above 25°C   | 1.56       | 0.38   | W/°C |
| $T_L$<br>$T_{PAK}$ | Maximum Temperature for Soldering Leads at 0.063in (1.6mm) from Case for 10 seconds, Package Body for 10 seconds | 300<br>260 |        | °C   |
| $T_J$ & $T_{STG}$  | Operating and Storage Temperature Range  | -55 to 150 |        |      |
| $R_{\theta JC}$    | Thermal Resistance, Junction-to-Case   | 0.64       | 2.6    | °C/W |
| $R_{\theta JA}$    | Thermal Resistance, Junction-to-Ambient  | 62         | 100    |      |

Caution: Stresses greater than those listed in the “Absolute Maximum Ratings” may cause permanent damage to the device.

**Electrical Characteristics**  $T_J = 25^{\circ}\text{C}$  unless otherwise specified


| Symbol       | Parameter                                | Min. | Typ. | Max. | Unit     | Test Conditions                                   |
|--------------|--|------|------|------|----------|---|
| $BV_{DSS}$   | Drain-to-Source Breakdown Voltage        | 500  | --   | --   | V        | $V_{GS}=0V, I_D=250\mu A$                         |
| $I_{DSS}$    | Drain-to-Source Leakage Current          | --   | --   | 1    | $\mu A$  | $V_{DS}=500V, V_{GS}=0V$                          |
|              |  | --   | --   | 100  |          | $V_{DS}=400V, V_{GS}=0V, T_J=125^{\circ}\text{C}$ |
| $I_{GSS}$    | Gate-to-Source Leakage Current           | --   | --   | +100 | nA       | $V_{GS}=30V, V_{DS}=0V$                           |
|              |  | --   | --   | -100 |          | $V_{GS}=-30V, V_{DS}=0V$                          |
| $R_{DS(ON)}$ | Static Drain-to-Source On-Resistance     | --   | 0.40 | 0.48 | $\Omega$ | $V_{GS}=10V, I_D=6.5A$                            |
| $V_{GS(TH)}$ | Gate Threshold Voltage                   | 2.0  | --   | 4.0  | V        | $V_{DS}=V_{GS}, I_D=250\mu A$                     |
| $g_{fs}$     | Forward Transconductance                 | --   | 15   | --   | S        | $V_{DS}=30V, I_D=13A$                             |
| $C_{iss}$    | Input Capacitance                        | --   | 2150 | --   | pF       | $V_{GS}=0V, V_{DS}=25V, f=1.0MHz$                 |
| $C_{rss}$    | Reverse Transfer Capacitance             | --   | 23   | --   |          |   |
| $C_{oss}$    | Output Capacitance                       | --   | 210  | --   |          |   |
| $Q_g$        | Total Gate Charge                        | --   | 45   | --   | nC       | $V_{DD}=250V, I_D=13A, V_{GS}=0 \text{ to } 10V$  |
| $Q_{gs}$     | Gate-to-Source Charge                    | --   | 10   | --   |          |   |
| $Q_{gd}$     | Gate-to-Drain (Miller) Charge            | --   | 18   | --   |          |   |
| $t_{d(ON)}$  | Turn-on Delay Time                       | --   | 15   | --   | ns       | $V_{DD}=250V, I_D=13A, V_{GS}=10V, R_g=6.1\Omega$ |
| $t_{rise}$   | Rise Time                                | --   | 25   | --   |          |   |
| $t_{d(OFF)}$ | Turn-Off Delay Time                      | --   | 45   | --   |          |   |
| $t_{fall}$   | Fall Time                                | --   | 35   | --   |          |   |
| $I_{SD}$     | Continuous Source Current <sup>[2]</sup> | --   | --   | 13   | A        | Integral pn-diode in MOSFET                       |
| $I_{SM}$     | Pulsed Source Current <sup>[2]</sup>     | --   | --   | 52   |          |   |
| $V_{SD}$     | Diode Forward Voltage                    | --   | --   | 1.5  | V        | $I_S=13A, V_{GS}=0V$                              |
| $t_{rr}$     | Reverse Recovery Time                    | --   | --   | --   | ns       | $V_{GS}=0V, I_F=13A, di/dt=100A/\mu s$            |
| $Q_{rr}$     | Reverse Recovery Charge                  | --   | 4.0  | --   | $\mu C$  |   |

**Note:**


[1]  $T_J=+25^{\circ}\text{C}$  to  $+150^{\circ}\text{C}$ 

[2] Pulse width $\leq 380\mu s$ ; duty cycle $\leq 2\%$ .


## Typical Characteristics(Cont.)




**Figure 2. Maximum Power Dissipation vs Case Temperature**




**Figure 3. Maximum Continuous Drain Current vs Case Temperature**



**Figure 4. Typical Output Characteristics**



**Figure 5. Typical Drain-to-Source ON Resistance vs Gate Voltage and Drain Current**



## Typical Characteristics(Cont.)

Figure 6. Maximum Peak Current Capability




Figure 7. Typical Transfer Characteristics




Figure 8. Unclamped Inductive Switching Capability




Figure 9. Typical Drain-to-Source ON Resistance vs Drain Current





Figure 10. Typical Drain-to-Source ON Resistance vs Junction Temperature



## Typical Characteristics(Cont.)

Figure 11. Typical Breakdown Voltage vs Junction Temperature




Figure 12. Typical Threshold Voltage vs Junction Temperature




Figure 13. Maximum Forward Bias Safe Operating Area




Figure 14. Typical Capacitance vs Drain-to-Source Voltage




Figure 15. Typical Gate Charge vs Gate-to-Source Voltage





Figure 16. Typical Body Diode Transfer Characteristics



## TestCircuitsandWaveforms




Fig. 1.1 Peak Diode Recovery  $dv/dt$  Test Circuit




Fig. 1.2 Peak Diode Recovery  $dv/dt$  Waveforms

## Test Circuits and Waveforms (Cont.)




Fig. 2.1 Switching Test Circuit




Fig. 2.2 Switching Waveforms




Fig. 3.1 Gate Charge Test Circuit




Fig. 3.2 Gate Charge Waveform




Fig. 4.1 Unclamped Inductive Switching Test Circuit





Fig. 4.2 Unclamped Inductive Switching Waveforms



## Package Dimension TO-220



| DIM.            | MILLIMETERS |       | INCHES |       |
|-----------------|-------------|-------|--------|-------|
|                 | MIN.        | MAX.  | MIN.   | MAX.  |
| A               | 4.25        | 4.65  | 0.167  | 0.183 |
| b               | 0.69        | 1.01  | 0.027  | 0.040 |
| b(1)            | 1.20        | 1.73  | 0.047  | 0.068 |
| c               | 0.36        | 0.61  | 0.014  | 0.024 |
| D               | 14.85       | 15.49 | 0.585  | 0.610 |
| E               | 10.04       | 10.51 | 0.395  | 0.414 |
| e               | 2.41        | 2.67  | 0.095  | 0.105 |
| e(1)            | 4.88        | 5.28  | 0.192  | 0.208 |
| F               | 1.14        | 1.40  | 0.045  | 0.055 |
| H(1)            | 6.09        | 6.48  | 0.240  | 0.255 |
| J(1)            | 2.41        | 2.92  | 0.095  | 0.115 |
| L               | 13.35       | 14.02 | 0.526  | 0.552 |
| L(1)            | 3.32        | 3.82  | 0.131  | 0.150 |
| $\varnothing P$ | 3.54        | 3.94  | 0.139  | 0.155 |
| Q               | 2.60        | 3.00  | 0.102  | 0.118 |

ECN: X12-0208-Rev. N, 08-Oct-12  
DWG: 5471


### Notes

\* M = 1.32 mm to 1.62 mm (dimension including protrusion)  
Heatsink hole for HVM

## REEL SPECIFICATION

| P/N      | PKG    | QTY                              |
|----------|--------|----------------------------------|
| MS13N50P | TO-220 | 1 tube of 50pcs/1 box of 1000pcs |

Package Dimension TO-220F



| Symbol | Dimensions In Millimeters |        | Dimensions In Inches |       |
|--------|---------------------------|--------|----------------------|-------|
|        | Min.                      | Max.   | Min.                 | Max.  |
| A      | 4.300                     | 4.700  | 0.169                | 0.185 |
| A1     | 1.300 REF.                |        | 0.051 REF.           |       |
| A2     | 2.800                     | 3.200  | 0.110                | 0.126 |
| A3     | 2.500                     | 2.900  | 0.098                | 0.114 |
| b      | 0.500                     | 0.750  | 0.020                | 0.030 |
| b1     | 1.100                     | 1.350  | 0.043                | 0.053 |
| b2     | 1.500                     | 1.750  | 0.059                | 0.069 |
| c      | 0.500                     | 0.750  | 0.020                | 0.030 |
| D      | 9.960                     | 10.360 | 0.392                | 0.408 |
| E      | 14.800                    | 15.200 | 0.583                | 0.598 |
| e      | 2.540 TYP.                |        | 0.100 TYP.           |       |
| F      | 2.700 REF.                |        | 0.106 REF.           |       |
| $\Phi$ | 3.500 REF.                |        | 0.138 REF.           |       |
| h      | 0.000                     | 0.300  | 0.000                | 0.012 |
| h1     | 0.800 REF.                |        | 0.031 REF.           |       |
| h2     | 0.500 REF.                |        | 0.020 REF.           |       |
| L      | 28.000                    | 28.400 | 1.102                | 1.118 |
| L1     | 1.700                     | 1.900  | 0.067                | 0.075 |
| L2     | 1.900                     | 2.100  | 0.075                | 0.083 |

REEL SPECIFICATION

| P/N      | PKG     | QTY                              |
|----------|---------|----------------------------------|
| MS13N50F | TO-220F | 1 tube of 50pcs/1 box of 1000pcs |

## Attention

■ Any and all MSKSEMI Semiconductor products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your MSKSEMI Semiconductor representative nearest you before using any MSKSEMI Semiconductor products described or contained herein in such applications.

■ MSKSEMI Semiconductor assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specification of any and all MSKSEMI Semiconductor products described or contained herein.

■ Specifications of any and all MSKSEMI Semiconductor products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.

■ MSKSEMI Semiconductor strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.

■ In the event that any or all MSKSEMI Semiconductor products (including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.

■ No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of MSKSEMI Semiconductor.

■ Information (including circuit diagrams and circuit parameters) herein is for example only ; it is not guaranteed for volume production. MSKSEMI Semiconductor believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringement of intellectual property rights or other rights of third parties.

■ Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the MSKSEMI Semiconductor product that you intend to use.