




NOTES:
1.Rating : 10A 250VAC
2.Contact resistance : 50mΩ Max
3.Insulation resistance : >100MΩ (Min) 500VDC
4.Dielectric strength : >2000VAC 0.5mA 1 minutes

5	→	10	→	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM		
4	→	9	→	RANGE	TOLERANCE				GYW 2019.04.03	SCALE	NO		
3	→	8	→	X	±0.30					MAT'L	***		
2	→	7	→	X.X	±0.20					MATERIAL NO.			
1	→	6	→	X.XX	±0.10								
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±1°	东莞市六钧电子五金有限公司				RT-C02-W1		*****	A0