








Specifications:
规格:
Voltage rating:250V AC/DC
额定电压: 250V AC/DC
Current rating:7A AC/DC
额定电流: 7A AC/DC
Withstanding voltage:1500V AC/minute
耐受电压: 1500V AC/分钟
Temperature range:-40℃~+85℃
温度范围: -40℃~+85℃
Insulation resistance:1000MΩ min
绝缘电阻: 1000MΩ Min
Contact resistance:10mΩ Max
接触电阻: 10mΩ Max




- X9396 W R - XX A- 46 V01
① ② ③ ④ ⑤ ⑥ ⑦
- 1.Series No
 - 2.Category:W-Wafer
 - 3.Welding Board Range:V-Stright 180°
 - 4.Row No.Pin No:XX-02~15 Pin
 - 5.Special No:A-There are graps
 - 6.Material:46-PA46 UL94V-0
 - 7.Plating:V01-Gold 1u"

2Pin为1个进胶点, 3Pin和3Pin以上为2个进胶点



PCB LAYOUT



Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
02	3.96	7.92	09	31.68	35.64
03	7.92	11.88	10	35.64	39.60
04	11.88	15.84	11	39.60	43.56
05	15.84	19.80	12	43.56	47.52
06	19.80	23.76	13	47.52	51.48
07	23.76	27.72	14	51.48	55.44
08	27.72	31.68	15	55.44	59.40

X9396WR-XXA-46V01	PA46	Brass	Gold 1u"	X9396H
PART NO	Material	Material(Pin)	Finish	Suitable XKB Housing

					ANGLAR	±5°
Δx					L≤ 4	±0.2
Δx					4<L≤ 16	±0.3
Δx					16<L≤ 63	±0.4
MARK					L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE: 3.96mm Crimp Style Connector		
DWN		VIEW:	PART NO.: X9396WR-XXA-46V01		
CHKD		UNIT: mm/in	DWG NO.: X-X9396WR-XXA-46V01		
APPD		SIZE: A4	WEIGHT	SHEET	REVISION
				1/1	A0