


## YHJ-65H225SERIES:

### Description

YHJ-65H225 series are integrated GaNFET which possesses not only E-mode GaN's benefits but also compatibility with commonly-seen e-mode GaN, Cascode GaN and Si MOSFET. YHJ-65H225 series provides high breakdown voltage, high current and high operating speed which is suitable for high power applications.

### Features


- Gate drive voltage compatibility (-10V to 15V)
- High operating frequency
- Zero reverse recovery loss



### Applications

- Switch Mode Power Supplies (SMPS)
- AC-DC/ DC- DC Converters
- Motor Drives

### Typical Application Circuit



### Ordering information:

Ordering Code	PACKAGE	Marking (Product Code)	Applications	MPQ
YHJ - 65H225ADI	DFN8*8mm	65H225ADI	Industrial	2500PCS
YHJ-65H225DDI	DFN5*6mm	65H225DDI	Industrial	3000PCS
YHJ-65H225AMC	DFN8*8mm	65H225AMC	Consumer	2500PCS
YHJ-65H225DDC	DFN5*6mm	65H225DDC	Consumer	3000PCS

## Table of Contents

	Description .....	1
	Features .....	1
	Applications .....	1
	Top View .....	1
	Typical Application Circuit .....	1
	Ordering Information .....	1
1	Electrical Characteristics and Parameters .....	2
2	Typical Characteristic Curves .....	5
3	Package Outline Dimensions .....	7
4	Package Marking Description .....	11
5	Change Log .....	12

## 1、Electrical Characteristics

➤ **Table 1** Absolutemaximumratings

Symbol	Parameter	Value	Unit
$V_{DSS}$	Drain-source voltage	650	V
$V_{(TR)DSS}$	Transient drain to source voltage <sup>a</sup>	800	V
$V_{GSS}$	Gate- source voltage	-10V ~ +15V	V
$P_{tot}$	Total power dissipation @ $T_c = 25^\circ\text{C}$	63	W
$I_D$	Drain current (continuous) at $T_c = 25^\circ\text{C}$ operation	8	A
	Drain current (continuous) at $T_c = 100^\circ\text{C}$ operation	5	A
$I_{DM}$	Pulsed drain current (pulse width: 100us)	13	A
$T_J$	Operating temperature	-55 to +150	$^\circ\text{C}$
$T_S$	Storage temperature	-55 to +150	$^\circ\text{C}$
$T_{SOLD}$	Soldering peak temperature <sup>e</sup>	260	$^\circ\text{C}$

a. In off-state, spike duty cycle  $D < 0.01$ , spike duration  $< 1\mu\text{s}$

b. For increased stability at high current operation, see Circuit Implementation on page 3

c. Continuous switching operation

d.  $\leq 300$  pulses per second for a total duration  $\leq 20$  minutes

e. For 10 sec., 1.6mm from the case

➤ **Table 2** ThermalCharacteristics

Symbol	Parameter	Value	Unit
$R_{\theta JA}$	Thermal resistance junction-ambient	42	$^\circ\text{C}/\text{W}$
$R_{\theta JC}$	Thermal resistance junction-case	2.1	$^\circ\text{C}/\text{W}$

**Table 3 Electrical Characteristics (T<sub>CASE</sub> = 25 °C unless otherwise stated)**

Symbol	Parameter	Conditions	Values			Unit
			min.	typ.	max.	
V <sub>(BL)DSS</sub>	Drain-source voltage	V <sub>GS</sub> =0V	650	-	-	V
V <sub>GS(th)</sub>	Gate threshold voltage	V <sub>DS</sub> = 10V ,I <sub>D</sub> =1mA	1.2	1.6	2.0	V
R <sub>DS(on)</sub>	Static drain-source on-resistance	V <sub>GS</sub> =10V, I <sub>D</sub> =5A, T <sub>J</sub> =25 °C	-	215	250-	mΩ
		V <sub>GS</sub> =10V, I <sub>D</sub> =5A, T <sub>J</sub> =150 °C	-	475	-	
I <sub>DSS</sub>	Drain-source leakage current	V <sub>GS</sub> =0V, V <sub>DS</sub> =650V, T <sub>J</sub> =25°C	-	0.5	12	μA
		V <sub>GS</sub> =0V, V <sub>DS</sub> =650V, T <sub>J</sub> =150°C	-	100	-	
C <sub>ISS</sub>	Input capacitance	V <sub>GS</sub> =0V, V <sub>DS</sub> =400V, f=1MHz	-	90	-	pF
C <sub>OSS</sub>	Output capacitance		-	50	-	
C <sub>RSS</sub>	Reverse transfer capacitance		-	1	-	
Q <sub>G</sub>	Gate charge	V <sub>GS</sub> =0~10V, V <sub>DS</sub> =400V, I <sub>DS</sub> =10A	-	1.6	-	nC
Q <sub>GS</sub>	Gate-source charge		-	0.5	-	
Q <sub>OSS</sub>	Output charge	V <sub>GS</sub> =0V, V <sub>DS</sub> =0~400V	-	14	-	nC
t <sub>D(on)</sub>	Turn-on delay time	V <sub>DS</sub> =400V, V <sub>GS</sub> =0 to 12V, I <sub>DS</sub> =7A ,R <sub>G</sub> =25Ω	-	3.5	-	ns
t <sub>D(off)</sub>	Turn-off delay time		-	7	-	
Q <sub>RR</sub>	Reverse recovery charge	V <sub>GS</sub> =-10V, V <sub>DS</sub> =0V	-	0	-	nC

## 2、Typical Characteristic Curves

Figure 1. On-Region Characteristics ( $T_j=25\text{ }^\circ\text{C}$ )




Figure 2. On-Region Variation with Temperature




Figure 3. On-Resistance vs Drain Current and Temperature




Figure 4. Transfer Characteristics




Figure 5. On-Resistance with Gate to Source Voltage




Figure 6. Capacitance Characteristics






Figure 7. Gate Charge Characteristics




Figure 8. Threshold Voltage with Temperature




Figure 9. Reverse Conduction Characteristics (Tj=25 °C)






Fig 10. Reverse Conduction Characteristics (Tj=150 °C)




### 3、Package Outline Dimensions

- DFN-8\*8



#### DFN-8X8 Recommended PCB Soldering Footprint




Ref.	Dimensions(in mm)			Ref.	Dimensions(in mm)		
	Min.	Typ.	Max.		Min.	Typ.	Max.
A	0.8	0.9	1	D3	0.4	0.5	0.6
A1	0	-	0.2	E1	2.7	2.8	2.9
b	0.9	1	1.1	E2	3.1	3.2	3.3
D	7.9	8	8.1	E3	0.9	1	1.1
E	7.9	8	8.1	e	2BSC		
D1	6.9	7	7.1	L	0.4	0.5	0.6
D2	6.9	7	7.1				

**NOTE:**


1. ALL DIMENSIONS ARE IN MM.
2. DIMENSIONS ARE NOT INCLUSIVE BURRS AND MOLD FLASH.

**(CeramicDFN 8\*8 4L EP1 S/Ceramic DFN 8\*8 8L)**

**EP1 S Carrier Tape**




**DFN 8\*8 4L EP1 S/Ceramic DFN 8\*8 8L EP1 S Reel**






● DFN-5\*6



**DFN-8X8 Recommended PCB Soldering Footprint**




Ref.	Dimensions(in mm)			Ref.	Dimensions(in mm)		
	Min.	Typ.	Max.		Min.	Typ.	Max.
A	0.8	0.9	1	D3	0.15	0.25	0.35
A1	0	-	0.3	E1	2	2.1	2.2
b	0.65	0.75	0.85	E2	1.95	2.05	2.15
D	4.9	5	5.1	E3	0.75	0.85	0.95
E	5.9	6	6.1	e	1.25BSC		
D1	4.4	4.5	4.6	L	0.4	0.5	0.6
D2	4.16	4.26	4.36				

**NOTE:**  
 1. ALL DIMENSIONS ARE IN MM.  
 2. DIMENSIONS ARE NOT INCLUSIVE BURRS AND MOLD FLASH.




DFN5x6 Carrier Tape



UNIT: MM

PACKAGE	A0	B0	K0	D0	D1	E	E1	E2	P0	P1	P2	T
DFN5x6 (12 mm)	6.30 ±0.10	5.45 ±0.10	1.30 ±0.10	1.50 MIN.	1.55 ±0.05	12.00 ±0.30	1.75 ±0.10	5.50 ±0.10	8.00 ±0.10	4.00 ±0.10	2.00 ±0.10	0.30 ±0.05

DFN5x6 Reel




UNIT: MM

TAPE SIZE	REEL SIZE	M	N	W	W1	H	K	S	G	R	V
12 mm	φ330	φ330.00 ±0.50	φ97.00 ±0.10	13.00 ±0.30	17.40 ±1.00	φ13.00 +0.50 -0.20	10.60	2.00 ±0.50	---	---	---


DFN5x6 Tape

Leader / Trailer & Orientation

Unit Per Reel:  
3000pcs



#### 4、 Package Marking Description



NOTE:	
LOGO	-Company Logo
NITRIDE	-Company Name
65H225	-Part Number
D	-Package Size
C	-Package Type
C	-Applications
B300	-Material & Lot No.
2220	- <b>Date code</b> YYWW

## 5、Change Log

Version	Date	Description
V1.0	August 26, 2022	Initial version

- **Note:YHJ semiconductor reserves the right to revise products and/or specifications without notice.**