









Recommend P.C.B Layout
General Tolerance±0.05



Specifications:
规格:
Voltage rating:600V AC/DC
额定电压: 600V AC/DC
Current rating:9A AC/DC
额定电流: 9A AC/DC
Withstanding voltage:1500V AC/minute
耐受电压: 1500V AC/分钟
Temperature range:-25℃~+85℃
温度范围: -25℃~+85℃
Insulation resistance:≥1000MΩ
绝缘电阻: ≥1000MΩ
Contact resistance:≤10mΩ
接触电阻: ≤10mΩ
After environmental testing:≤20mΩ
环境测试后: ≤20兆欧

X9357 W R X-XX S-XXSNXX
01 02 03 04 05 06 07 08 09

01 Series No.
02 Category:W-wafer
03 Welding Board Angle: R-Right Angle 90'
04 Welding Way: Blank-DIP;
05 Row No.-Pin No.: XX-Single row
06 Special NO.: S-With positioning column
07 Material:N0-PA66 94V-0;
N2-PA66 94V-2
08 Planting Category: SN-Bright tin plating
09 Color:E Blank-natural color ;BK-Black

Poles	Dimensions(mm)	
	A	B
02	4.20	9.60
03	8.40	13.80
04	12.60	18.00
05	16.80	22.20
06	21.00	26.40

X9357WR-XXS-N2SNBK	Nylon 66 UL94V-2 (Black)	Brass	Tin-Plated	X9357H
X9357WR-XXS-N0SN	Nylon 66 UL 94V-0			
X9357WR-XXS-N2SN	Nylon 66 UL 94V-2			
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Terminal

广东星坤科技股份有限公司

文件工程章

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
Δ建					ANGULAR ±5°
Δ数					L≤ 4 ±0.2
ΔX					4<L≤ 16 ±0.3
					16<L≤ 63 ±0.4
					L> 63 ±0.5

XKLB

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND	SCALE: N/A	MODEL TYPE: 4.2mm Crimp Style Connector
DWN	VIEW:	PART NO.: X9357WR-XXS-N0SN
CHKD	UNIT: mm/in	DWG NO.: X-X9357WR-XXS-N0SN
APPD	SIZE: A4	WEIGHT SHEET REVISION
		1/1 A0