








(Ø0.60)PICK&PLACE AREA



SOLDER AREA





3D VIEW




(0.04)WORKING HEIGHT

(0.07)MAX.HEIGHT



RECOMMENDED PCB LAYOUT
TOLERANCE±0.05(焊盘推荐图)



METAL MASK T=0.10
TOLERANCE±0.05(钢网推荐图)

NOTES

- (1)MATERIAL:C5210 THICKNE=0.10mm
- (2)PRODUCT SPECIFICATIONS:
 - 2-1:RATED CURRENT: 1.0A
 - 2-2:VOLTAGE RATING: 1.50V
 - 2-3:CONTACT RESISTANCE: 80mΩ/MAX
 - 2-4:WELDING THRUST:≥ 3KG
 - 2-5:OPERATING TEMPERATURE: -40°C~+85°C
 - 2-6:DURABILITY: 1500 CYCLES
- (3):SALT SPRAY: 72 HOURS
- (4):FINISH:50u"Min NICKEL UNDERPLATING OVER ALL.
- (5):REQUIREMENTS
 - 5-1:TERMINAL TO EAT FULL TIN,NOTPEELING
WELDING OBVIOUS COLOR AND OTHED ADVERSE
 - 5-2:ROHS,REACH,HF HALOGER ADVERSE OF DOMESTIC
AND INTERNATIONAL ENVIRONMNTAL REQUIREMENTS



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.' ±2' X.X' ±0.5'	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 天线弹片 L1.90*W1.0*H2.6
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW-TXT191026AJ
UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: HYC-2406081156
			SHEET NO. 1 OF 1