






3D View



METAL MASK T=0.08

TOLERANCE:±0.05MM

(FOR REFERENCE ONLY)

(For Reference Only)
Stated At Compression

NOTES:

1:MATERIAL

1-1: SUS-301 THICKNE=0.10MM

2:SPECIFICATIONS

2-1: RATED CURRENT: 1.0A

2-2: VOLTAGE RATING: 1.5V

2-3: CONTACT RESISTANCE: 80mΩ/MAX

2-4: WELDING THRUST: ≥3KG

2-5: OPERATING TEMPERATURE: -40°C~+85°C

3:DURABILITY: 1500 CYCLES

4:SALT SPRAY TIME: 24H

5:ELECTROPLATE: THE NICKEL-PLATED SUBSTRATE IS 50u" MIN

6:REQUIREMENTS

6-1: TERMINAL TO EAT FULL TIN, NOT PEELING,
WELDING OBVIOUS COLOR AND OTHER ADVERSE6-2: ROHS, REACH, HF HALOGEN ADVERSE OF DOMESTIC
AND INTERNATIONAL ENVIRONMENTAL REQUIREMENTS

深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2" X.X' ±0.5"	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 天线弹片 L2. 55*W1. 2*H3. 5	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW-TXT2551235A	
 UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: HYC-2406081731	
			SHEET NO. 1 OF 1	