






3D View




STATED AT COMPRESSION
(FOR REFERENCE ONLY)



RECOMMENDED PCB LAYOUT
TOLERANCE±0.05(焊盘推荐图)



METAL MASK T=0.10
TOLERANCE±0.05(钢网推荐图)




NOTES

- (1) MATERIAL: SUS-304 THICKNESS=0.10mm
(2) PRODUCT SPECIFICATIONS:
2-1: RATED CURRENT: 1.0A
2-2: VOLTAGE RATING: 1.50V
2-3: CONTACT RESISTANCE: 80mΩ/MAX
2-4: WELDING THRUST: ≥ 3KG
2-5: OPERATING TEMPERATURE: -40°C~+85°C
2-6: DURABILITY: 1500 CYCLES
(3) SALT SPRAY: 24 HOURS
(4) REQUIREMENTS
4-1: TERMINAL TO EAT FULL TIN, NOT PEELING
WELDING OBVIOUS COLOR AND OTHER ADVERSE
4-2: ROHS, REACH, HF HALOGEN ADVERSE OF DOMESTIC
AND INTERNATIONAL ENVIRONMENTAL REQUIREMENTS



深圳市华宇创精密电子有限公司

TOLERANCE:		DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME:	
X.X ±0.30	X.XX ±0.25			天线弹片 L3.50*W1.5*H3.5	
X.XXX ±0.15		CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	HYCW-TXT351535A
X: ±2° X.X: ±0.5°				MOLD NO.	
		APPROVED BY:	DATE : 2014-02-23	DRAW NO:	HYC-2406081438
UNIT: mm [inch]				SHEET NO.	1 OF 1
SCALE:1:1	SIZE: A4	邱敏			