







CONTACT AREA



RECOMMENDED PCB LAYOUT  
TOLERANCE±0.05 (焊盘推荐图)



## NOTES

- (1) MATERIAL: SUS-304 THICKNESS=0.10mm
- (2) PRODUCT SPECIFICATIONS:
  - 2-1: RATED CURRENT: 1.0A
  - 2-2: VOLTAGE RATING: 1.50V
  - 2-3: CONTACT RESISTANCE: 80mΩ/MAX
  - 2-4: WELDING THRUST: 3Kgf
  - 2-5: OPERATING TEMPERATURE: -40°C~+85°C
  - 2-6: DURABILITY: 1500 CYCLES
- (3): SALT SPRAY: 24 HOURS
- (4): FINISH: 50u"Min NICKEL UNDERPLATING OVER ALL.
- (5): REQUIREMENTS
  - 5-1: TERMINAL TO EAT FULL TIN, NOT PEELING WELDING OBVIOUS COLOR AND OTHER ADVERSE
  - 5-2: ROHS, REACH, HF HALOGEN ADVERSE OF DOMESTIC AND INTERNATIONAL ENVIRONMENTAL REQUIREMENTS



深圳市华宇创精密电子有限公司

|                                                                           |                    |                      |                                    |                     |
|---------------------------------------------------------------------------|--------------------|----------------------|------------------------------------|---------------------|
| TOLERANCE:<br>X.X ±0.30<br>X.XX ±0.25<br>X.XXX ±0.15<br>X' ±2" X.X' ±0.5" | DRAWN BY :<br>陈一鸣  | DATE :<br>2014-02-23 | PART NAME:<br>天线弹片 L2.50*W1.0*H2.4 |                     |
|                                                                           | CHECKED BY:<br>马跃  | DATE :<br>2014-02-23 | PART NO.<br>HYCW-TXT251024A        | MOLD NO.            |
| UNIT: mm [inch]<br>SCALE: 1:1 SIZE: A4                                    | APPROVED BY:<br>邱敏 | DATE :<br>2014-02-23 | DRAW NO:<br>HYC-2406071458         | SHEET NO.<br>1 OF 1 |
|                                                                           |                    |                      |                                    |                     |