

SOT-23 Plastic-Encapsulate Transistors


S9012

PNP Transistors

Features

- High Collector Current
- Complementary To S9013
- Excellent hFE Linearity

Marking: 2T1



Maximum Ratings (T_a=25°C unless otherwise noted)

Symbol	Parameter	Value	Unit
V _{CBO}	Collector Base Voltage	-40	V
V _{CEO}	Collector Emitter Voltage	-25	V
V _{EBO}	Emitter Base Voltage	-5	V
I _c	Collector Current	-500	mA
P _c	Collector Power Dissipation	300	mW
T _j	Junction Temperature	150	°C
T _{stg}	Storage Temperature	-55 ~ +150	°C
R _{θJA}	Thermal Resistance From Junction To Ambient	416	°C/W

Electrical Characteristics (T_a=25°C unless otherwise specified)

Symbol	Parameter	Test Conditions	Min	Typ	Max	Unit
V _{(BR)CBO}	Collector-base breakdown voltage	I _C = -100μA, I _E = 0	-40			V
V _{(BR)CEO}	Collector-emitter breakdown voltage	I _C = -1mA, I _B = 0	-25			V
V _{(BR)EBO}	Emitter-base breakdown voltage	I _E = -100μA, I _C = 0	-5			V
I _{CBO}	Collector cut-off current	V _{CB} = -40V, I _E = 0			-100	nA
I _{CEO}	Collector cut-off current	V _{CE} = -20V, I _B = 0			-100	nA
I _{EBO}	Emitter cut-off current	V _{EB} = -5V, I _C = 0			-100	nA
h _{FE}	DC current gain	V _{CE} = -5V, I _C = -1mA	200			
		V _{CE} = -1V, I _C = -50mA	120		350	
V _{CE(sat)}	Collector-emitter saturation voltage	I _C = -500mA, I _B = -50mA			-0.6	V
V _{BE(sat)}	Base-emitter saturation voltage	I _C = -500mA, I _B = -50mA			-1.2	V
f _T	Transition frequency	V _{CE} = -6V, I _C = -20mA, f = 30MHz	150			MHz
C _{ob}	Collector output capacitance	V _{CB} = -10V, I _E = 0, f = 1MHz			5	pF

Typical Characteristics

