

Specification Sheet

Part Number: 170-03148

Flexible construction that conforms to irregular shapes and contours. Hook and loop feature wraps over cable bundle allowing future access to cables.

Easy access saves assembly time and allows for easy splicing or insertion of additional wires.

PET yarn construction offers excellent protection against cuts and abrasions.



Braided Sleeving, Hook & Loop, 0.5" Dia, PET, Black, 100 ft/bulk reel

Article Number	170-03148
----------------	-----------

Type	BSHKLP120B
------	------------

Color	Black (BK)
-------	------------

Quantity Per	reel
--------------	------

Product Description	Designed for the quick and easy management of wires, this expandable sleeving has an internal hook and loop strap that is able to adhere to its outer PET braid, delivering flexibility that allows it to fit around odd-shaped connectors. Its color-matched hook and loop closure provides for an easy on and off installation, as well as instant and convenient access for harness break-outs and networks. the primary application for this sleeving is the wrapping and bunching of cables in a deployed situation or when frequent access to cables is necessary.
---------------------	--

Short Description	Braided Sleeving, Hook & Loop, 0.5" Dia, PET, Black, 100 ft/bulk reel
Global Part Name	BSHKLP120B-PET-BK
Length L (Imperial)	100.0
Length L (Metric)	30.48
Bundle Diameter Min (Imperial)	0.1
Bundle Diameter Min (Metric)	2.54
Bundle Diameter Max (Imperial)	0.5
Bundle Diameter Max (Metric)	12.7
Diameter D (Imperial)	0.50
Diameter D (Metric)	12.7
Nominal Diameter (Imperial)	0.5
Nominal Diameter (Metric)	12.7
Wall Thickness WT (Imperial)	0.025
Wall Thickness WT (Metric)	0.635
Material	Polyester (PET)

Material Shortcut	PET
Flammability	FAR 25 UL 94 V-0
Halogen Free	Yes
UV Resistant (Yes/No)	No
Operating Temperature	-94°F to +257°F (-70°C to +125°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
UL Recognized (US)	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	30.48
Customs Number	5808100000

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

