

# 承認書

## SPECIFICATION FOR APPROVAL

客戶名稱  
CUSTOMER

客戶料號  
CUS. P/N

尺寸  
DIMENSION




**CRH-10.5x12.5x7.2**

編號  
SERIAL NO.

NO. CF1025657130

日期  
DATE

2023年5月12日

出圖 DRAWING		
發行 ISSUE	復核 CHECKED	核準 APPROVAL
		
DATE: 2023/5/12		

承認 CUSTOMER APPROVAL



东莞市灿峰电子有限公司

DONG GUAN CITY CAN FENG ELETRONICS CO., LTD

网址: www.canfengele.com E-mail: canfengdianzi@163.com

联系方式

王小姐: 13556646144

洪先生: 13809826886






# 承認書

## SPECIFICATION FOR APPROVAL

規格 ITEM	CRH-10.5x12.5x7.2		編號 SERIAL NO.	NO. CF1025657130	
1. 形狀尺寸 (單位mm) ; SHAPE & DIMENSION(unit/mm);  			A	10.50 ± 0.5      mm	
			B	12.50 ± 0.8      mm	
			C	7.20 ± 0.5      mm	
			D		
			E		
			F		
			G		
			2. 電器性能檢測項目 ELECTTRONICAL REQUIREMENTS;		
<input type="checkbox"/> L		TEST FREQ		測試儀器 TESTING INSTRUMENTS	
<input type="checkbox"/> Q		TEST FREQ	KHZ MHZ	1. Q-METER: <input type="checkbox"/> HP-4342A <input type="checkbox"/> MQ-172	
<input checked="" type="checkbox"/> Z	Z1=30 Ω MIN 25MHZ	KHZ	Z3=	KHZ MHZ	2. LCR-METER: <input type="checkbox"/> TH2826
	Z2=75 Ω MIN 100MHZ	KHZ	Z4=	KHZ MHZ	3. IMPEDANCE ANALYZER: <input checked="" type="checkbox"/> HP-4191A <input checked="" type="checkbox"/> Agilent 16092A <input type="checkbox"/> TH2826
溫度 TEMP	25±5℃	濕度 HUMIDITY	60±8%	4. L-METER: <input type="checkbox"/> TH-2775B	
繞線: WINDING	Z: Φ0.5*100L(mm)*0.5TS			5. DIGITAL MINI-OHM METER: VP2941A	
3. 外觀 THE LIMIT OF BREAKACE:					
項目 Item			標準值 Standard Value		
一處缺陷的面积 Area of a breakage			≤1mm <sup>2</sup>		
总缺陷面积 ALL area of the breakage			≤2mm <sup>2</sup>		
缺陷深度 The depth of the breakge			≤0.4mm		
毛刺长度 The length of burr			≤0.2mm		
4. 包裝 PACKAGING:  內包裝采用泡塑盒, 外包裝采用紙箱, 每箱產品外面都蓋上标签 (包括品名、數量、批號、檢驗員)。 Inner packing gdopts foam plastics box, outer packing adopts carton and each carton should have a qualified label outside(include the variey, quantity, batch number and inspector).					

# 檢 測 數 據

## INSPECTION DATA

規 格 ITEM	CRH-10.5x12.5x7.2					編 號 SERIAL NO.	NO. CF1025657130					
1. 形壯尺寸(单位/毫米): SHAPE & DIMENSION(unit/mm): =  							<input type="checkbox"/> L					
							<input type="checkbox"/> Q					KHZ MHZ
							<input checked="" type="checkbox"/> Z	Z1=30 Ω MIN	KHZ	Z1=	KHZ	
								Z2=75 Ω MIN	KHZ	Z4=	KHZ	
							溫 度 TEMP	25±5°C	濕 度 HUMIDITY	60±8%		
							繞 線: WINDING	Z: Φ 0.5*100L(mm)*0.5TS				
項 目 ITEM	電 氣 性 能 ELECTRONIC CHARACTERISTICS						尺 寸 DIMENSION(unit:mm)					
	Q	L(μH)	Z1(Ω)	Z2(Ω)	Z3(Ω)	Z4(Ω)	A	B	C	D	E	F
+			30	75			10.5	12.5	7.2			
-			0	0			0.5	0.8	0.5			
1			50.1	112.5			10.49	12.54	7.21			
2			49.6	111.6			10.46	12.51	7.22			
3			50.6	117.5			10.52	12.55	7.21			
4			50.4	116.3			10.48	12.66	7.24			
5			48.7	114.5			10.46	12.50	7.19			
6			52.1	111.2			10.54	12.68	7.18			
7			51.6	116.8			10.52	12.52	7.24			
8			50.8	117.3			10.54	12.56	7.24			
9			51.0	114.4			10.52	12.59	7.19			
10			52.1	114.2			10.51	12.64	7.20			
X			50.7	114.6			10.50	12.57	7.21			
Y/N			Y	Y			Y	Y	Y			
2. 測試儀器 TESTING INSTRUMENTS HP4191A+16092A  							檢 測 INSPECTION	復 核 CHECK	確 認 APPROVAL			
												


# 阻抗 - 頻率曲綫




IMPEDANCE V.S.FREQUENCY ( Z-Y )

規格 ITEM	CRH-10.5x12.5x7.2	編號 SERIAL NO.	NO. CF1025657130
------------	-------------------	------------------	------------------

材质特性：  
MATERIAL CHARACTERISTICS

材料 牌号 Material	初始磁 导率 Initial Permeability	比损耗因子 Relative Loss Factor	比温度系数 Relative Temperature Coefficient	饱和磁通密度 Saturation Magnetic Flux Density	剩磁 Reman- ence	矫顽力 Coercivi- ty	居里温度 Curie Tempera- ture	电阻率 Electric Resistiv- ity	使用范围 Applied Frequenc- y Range	密度 Densit- y
Unit symbol	$\mu$ $\pm 20\%$	$\tan \delta / \mu$ $\times 10^{-6}$	$\alpha \mu \gamma$ $\times 10^{-6}$	Bs (MT)	Br (MT)	HC (A/m)	Tc (°C)	$\rho$ ( $\Omega \cdot m$ )	F Mhz	d g/cm <sup>3</sup>
F2	650	20(0.1MHz)	2-5	330(1600A/m)	150	35	>110	>10 <sup>5</sup>	0.1-1.5	4.9



测试条件； TESTING CONDITION;	檢 測 INSPECTION	復 核 CHECK	确 認 APPROVAL
1. 测试仪器： HP 4191 A+16092 A Testing Equipment:			
2. 测试频率区间： 1MHZ-1000MHZ Testing Frequency Range:			
3. 测试绕组： Φ0.5*100L(mm)*0.5TS Testing Coil Specification:			