


SECTION A-A



SPECIFICATIONS

- Voltage rating: 250V AC, DC
- Current rating: 3A, AC/DC
- Withstanding voltage: 1000V AC/minute
- Insulation resistance: 1000M Ω /min
- Temperature range: -40℃ ~ +105℃
- Contact resistance: 20m Ω max

HOUSING

- Part No.: CS-2001-09A V2 W

V2: PA66 UL94V-2 W: White, 白色

- Poles: 02-16
- Material: Nylon 66, UL94V-2, White
- Q' TY: 1000 pcs/bag

1

2

3

4

5

6

7

8

Top view of the terminal block. It shows a rectangular housing with four terminals. Dimension C is the width of the housing, A is the distance between the centers of the terminals, and 2.50 is the distance between the centers of adjacent terminals.

Side view of the terminal block. It shows the profile of the housing and terminals. Dimension A is the height of the housing, and B is the width of the terminal block.

Front view of the terminal block. It shows the terminals and the housing. Dimension 5.60 is the height of the terminal block, 7.70 is the width of the terminal block, and 4.10 is the distance between the centers of adjacent terminals.

Cross-section A-A of the terminal block. It shows the internal structure of the housing and the terminals.

SECTION A-A

Bottom view of the terminal block. It shows the base of the housing and the terminals. Dimension 2.50 is the distance between the centers of adjacent terminals.

SPECIFICATIONS

- Voltage rating: 250V AC, DC
- Current rating: 3A, AC/DC
- Withstanding voltage: 1000V AC/minute
- Insulation resistance: 1000MΩ min
- Temperature range: -40℃ ~ +105℃
- Contact resistance: 20mΩ max

HOUSING

- Part No. : CS-2001-09A V2 W

Diagram showing the housing code V2:PA66 UL94V-2 and W:White, 白色.

- Poles: 02-16
- Material: Nylon 66, UL94V-2, White
- Q' TY: 1000 pcs/bag

RoHS2.0