




DURABILITY : 750 CYCLES MIN.
MATING FORCE : 23N MAX.
OPERATING TEMPERATURE: -40°C~+85°C.
STORAGE TEMPERATURE: -40°C~+85°C.
ALL CRITICAL DIMENSIONS WITH "*"

1. Turn ratio: 1~2: J1~J2=1CT:1CT($\pm 2\%$).
3~6: J3~J6=1CT:1CT($\pm 2\%$).
2. OCL: 350uH Min. at 100KHz 100mV 8mA DC.
3. Insertion Loss: -1.0 dB Max 1~100MHz.
4. Return loss: -20dB Min 1~10MHz;
-16dB Min 10~30MHz.
-12dB Min 30~60MHz.
-10dB Min 60~80MHz.
5. Cross talk: -40dB Min 1~30MHz;
-35dB Min 30~60MHz;
-30dB Min 60~100MHz;
6. CMR: -30dB Min 1~100MHz;
7. Hi-Pot: 1500V AC & 2250V DC
6S 1mA PRI TO SEC



					TOLERANCE UNLESS SPECIFIED														
					UP TO 5mm: ±0.1	ANGULAR ±1°	A0	2022.7.18	初次发行			WM							
					ABOVE 5mm: ±0.2		NO	DATE	REVISIONS			BY	APPD						
4	TERMINAL	PHOSPHOR BRONZE	8	6U”Au-PLATED(CONTACT AREA)	TITLE: PCB JACK				UNIT : MM	ROHS	DWN								
3	SHIELD	BRASS	1	Ni-PLATED	MODEL: PCB-832E				SCALE: 1:1	COMPLIANT	CHK'D								
2	TERMINALS BRACKET	PA9T(UL94V-0)	1	BLACK	东莞市六钧电子五金有限公司								APPD						
1	HOUSING	PA9T(UL94V-0)	1	BLACK															
NO.	PART NAME	MATERIAL	QTY	FINISHING															
PRO.AGL:   REV :A0																			