



SPECIFICATION

1. Rating: DC 12V 0.3A
2. Function: 2P2T
3. Contact Resistance:  $\leq 70m\Omega$  MAX
4. Operating Force:  $180\pm 80gf$ ,  $250\pm 100gf$
5. Life test: 10,000 cycles

P.C.B. LAYOUT

				TOLERANCE UNLESS SPECIFIED									
				UP TO 5mm: $\pm 0.1$	ANGULAR	1							
				ABOVE 5mm: $\pm 0.2$	$\pm 1^\circ$	NO	DATE	REVISIONS		BY	APPD		
4	SPRING	SUS	1	NATURAL	TITLE: VERTICAL PUSH SWITCH		UNIT : MM	ROHS	DWN				
3	CASE	PA66/0.3mm BRASS	1	GREY/Ag PLATED	MODEL: PB-22E60PA-N-E		SCALE: 5:1	COMPLIANT	CHK'D				
2	COVER	PA66	1	BLACK	东莞市六钧电子五金有限公司							APPD	
1	KNOB	PA66/0.045mm PBS	1	WHITE/BLACK/Ag CLAD								PRO.AGL:	
NO.	PART NAME	MATERIAL	QTY	FINISHING									