






REV	DATE	ECN NO.	MODIFICATION	APPROVER
A	2016/10/14		NEW	Jason_Lee
A1	2017/05/15	RD00317051501	SIZE CHANGE	Jason_Lee

NOTES:
MATERIAL:
Housing: High Temperature thermoplastic,UL94V-0
Terminal:Copper Alloy
Shell:Stainless
SPECIALTY:
Rated Current:0.5A MAX
Rated Voltage:50V
Ambient Temperature Range:-40°C~+85°C
Ambient Humidity Range :95% R.H. Max.
Contact Resistance:100mΩ Max
Insulation Resistance:1000MΩ/250V DC
Dielectric Withstanding Voltage:500V AC
Durability:5000 cycles
Temperature 260±5°C,




1.此为CD PIN, 此PIN无须时不需要设计PCB焊盘
2.此为CD PIN, 支持热插拔有需要可设计此功能





1.此为CD PIN, 此PIN无须时不需要设计PCB焊盘
2.此为CD PIN, 支持热插拔有需要可设计此功能

RECOMMENDED PCB LAYOUT
GENERAL TOLERANCE±0.05



IM pin Assignment	
IN#	Name
C1	VCC
C2	RST
C3	CLK
C5	GND
C6	VPP
C7	I/O



GENERAL TOLERANCE		UNITS mm	NAME: MICRO SIM CARD 6P PUSH PUSH	MyAntenna [®] 深圳市摩天射频技术有限公司 ShenZhen MyAntenna RF Technology Co., Ltd
SELECT	TOL			
X,XXX	±0.10±0.05±0.15	✓	APPD:	A-MicroSIM-1.35B
X,XX	±0.15±0.13±0.25		CHKD:	
X,X	±0.20±0.22±0.5		DR:	JACK
X	±0.30±0.38±1.00			
ANGLE	±2°			
			SCALE	SHEET
			1:1	1/1
			REV	A1