





3D View




NOTES:

- 1: MATERIAL
 - 1-1: YCUT-FX-EH THICKNE=0.08MM
- 2: SPECIFICATIONS
 - 2-1: RATED CURRENT: 1.0A
 - 2-2: VOLTAGE RATING: 5.0V
 - 2-3: CONTACT RESISTANCE: 50mΩ/MAX
 - 2-4: WELDING THRUST: ≥3KG
 - 2-5: OPERATING TEMPERATURE: -40°C~+85°C
- 3: DURABILITY: 20000 CYCLES
- 4: SALT SPRAY TIME: 48H
- 5: ELECTROPLATE: THE NICKEL-PLATED SUBSTRATE IS 60-120u"
- 6: REQUIREMENTS
 - 6-1: TERMINAL TO EAT FULL TIN, NOT PEELING, WELDING OBVIOUS COLOR AND OTHER ADVERSE
 - 6-2: ROHS, REACH, HF HALOGEN ADVERSE OF DOMESTIC AND INTERNATIONAL ENVIRONMENTAL REQUIREMENTS



RECOMMENDED PCB LAYOUT
TOLERANCE: ±0.05MM (FOR REFERENCE ONLY)



(For Reference Only)
Stated At Compression



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2' X.X' ±0.5'	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 天线弹片 L3.40*W1.0*H2.5
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW-TXT341025AJ
UNIT: mm [inch]	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: HYC-2406081014
SCALE: 1:1	SIZE: A4		SHEET NO. 1 OF 1