






Specifications:  
 规格:  
 Voltage rating: 100V AC/DC  
 额定电压: 100V AC/DC  
 Current rating: 1A AC/DC  
 额定电流: 1A AC/DC  
 Withstanding voltage: 300V AC/minute  
 耐受电压: 300V AC/分钟  
 Temperature range: -40°C~+105°C  
 温度范围: -40°C~+105°C  
 Insulation resistance: ≥100MΩ  
 绝缘电阻: ≥100MΩ  
 Contact resistance: ≤20mΩ  
 接触电阻: ≤20mΩ

X1004 W R S - XX A HF - 4T SW  
 ① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨


- Series No
- Category: W-Wafer
- Welding Board Angle: R-Stright 90°
- Welding Way: S-SMT
- Row No. Pin No: XX-02-15 Pin
- Special No: A-Inner Lock
- HF-Halogen Free
- Material: 4T-PA4T UL94V-0
- Plating: SW-Matte Tin Plating 100u" Min. overall, Ni 50u" Min. under Plating V01-Gold Flash overall, Ni 50u Min under Plating



X1004WRS-XXAHF-4TSW  
02-05Pin



Recommended PCB Layout: ±0.05



Poles	Dimensions(mm)			
	A	B	C	D
02	4.00	1.00	3.20	2.45
03	5.00	2.00	4.20	3.45
04	6.00	3.00	5.20	4.45
05	7.00	4.00	6.20	5.45
06	8.00	5.00		6.45
07	9.00	6.00		7.45
08	10.00	7.00		8.45
09	11.00	8.00		9.45
10	12.00	9.00		10.45
11	13.00	10.00		11.45
12	14.00	11.00		12.45
13	15.00	12.00		13.45
14	16.00	13.00		14.45
15	17.00	14.00		15.45

X1004WRS-XXAHF-4TSW	PA4T	Phosphor Bronze	X1004H-A
PART NO	Material	Material(Pin)	Suitable XKB Housing

X1004WRS-XXAHF-4T SW  
06-15Pin

广东星坤科技股份有限公司

Δ*	日期
Δx	日期
Δx	日期

MARK DESCRIPTION REVISIONS DATE REVISED APPROVED

ANGLAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5
UNSPECIFIED TOLERANCES	



XKB INDUSTRIAL PRECISION CO., LIMITED

DSND	SCALE: N/A	MODEL TYPE: 1.0mm Crimp Style Connector
DWN	VIEW:	PART NO.: X1004WRS-XXAHF-4TSW
CHKD	UNIT: mm/in	DWG NO.: X-X1004WRS-XXAHF-4TSW
APPD	SIZE: A4	WEIGHT SHEET REVISION 1/1 A0