


**Product Summary**

$V_{DS}$	$R_{DS(ON\_MAX)}$		$I_{D\_MAX}$
100 V	3.4 m $\Omega$	@ $V_{GS} = 10V$ TO263-3L	186 A
	3.6 m $\Omega$	@ $V_{GS} = 10V$ TO220-3L	

TO220-3L




Top View


TO263-3L



Top View



PIN Configuration  
(Top View)



Schematic Diagram

**Features**

- Low On-Resistance
- Excellent FoM (figure of merit)
- 100% UIS and  $R_g$  tested



**Applications**

- DC/DC in Telecoms and Industrial
- Synchronous Rectification in SMPS
- Hard Switching and High Speed Circuit

**Mechanical Data**

- Green Molding Compound
- Moisture Sensitivity: Level 1 per J-STD-020
- UL Flammability Classification Rating 94V-0

**Ordering Information**

Orderable Part Number	Package Type	Device Marking	Form	Quantity (pcs)
MX10T03AHS	TO220-3L	10T03AH	Tube	50
MX10T03AHT	TO263-3L	10T03AH	13" Tape&Reel	1,000

**Maximum Ratings** (@  $T_C = 25^\circ C$ , unless otherwise specified.)

Parameter	Symbol	Value	Unit
Drain - Source Voltage	$V_{DS}$	100	V
Gate - Source Voltage	$V_{GS}$	$\pm 20$	V
Continuous Drain Current ( $V_{GS} = 10V$ ) <sup>(1)</sup>	$I_D$	$T_C = 25^\circ C$	186
		$T_C = 100^\circ C$	132
Pulsed Drain Current <sup>(2)</sup>	$I_{DM}$	744	A
Single Pulse Avalanche Energy <sup>(3)</sup>	$E_{AS}$	960	mJ
Single Pulse Avalanche Current ( $L = 0.1mH$ )	$I_{AS}$	74	A
Power Dissipation	$P_D$	$T_C = 25^\circ C$	254
		$T_C = 100^\circ C$	127
Junction & Storage Temperature Range	$T_J, T_{STG}$	-55 ~ +175	$^\circ C$

**Thermal Characteristics**

Parameter	Symbol	Typ.	Max.	Unit
Thermal Resistance, Junction-to-Ambient <sup>(4)</sup>	$R_{\theta JA}$	30	35	$^\circ C/W$
Thermal Resistance, Junction-to-Case <sup>(5)</sup>	$R_{\theta JC}$	0.45	0.59	$^\circ C/W$

**Electrical Characteristics** (@  $T_J = 25^\circ\text{C}$ , unless otherwise specified.)

Parameter	Symbol	Test Condition	Min.	Typ.	Max.	Unit	
<b>Off Characteristics</b> <sup>(6)</sup>							
Drain-Source Breakdown Voltage	$V_{(BR)DSS}$	$V_{GS} = 0V, I_D = 250\mu A$	100	-	-	V	
Zero Gate Voltage Drain Current	$I_{DSS}$	$V_{DS} = 100V, V_{GS} = 0V$ $T_J = 125^\circ\text{C}$	-	-	1.0	$\mu A$	
			-	-	100	$\mu A$	
Gate-Source Leakage Current	$I_{GSS}$	$V_{GS} = \pm 20V, V_{DS} = 0V$	-	-	$\pm 100$	nA	
<b>On Characteristics</b> <sup>(6)</sup>							
Gate Threshold Voltage	$V_{GS(th)}$	$V_{GS} = V_{DS}, I_D = 250\mu A$	2.0	3.0	4.0	V	
Static Drain-Source On-Resistance	$R_{DS(on)}$	$V_{GS} = 10V, I_D = 20A$	TO263-3L	-	2.8	3.4	m $\Omega$
			TO220-3L	-	3.0	3.6	m $\Omega$
Forward Transconductance	$g_{fs}$	$V_{DS} = 5.0V, I_D = 20A$	-	54	-	S	
Diodes Forward Voltage	$V_{SD}$	$I_S = 2.0A, V_{GS} = 0V$	-	0.7	1.2	V	
<b>Dynamic Characteristics</b> <sup>(7)</sup>							
Input Capacitance	$C_{iss}$	$V_{DS} = 50V, V_{GS} = 0V, f = 1\text{MHz}$	-	4406	-	pF	
Output Capacitance	$C_{oss}$		-	1621	-	pF	
Reverse Transfer Capacitance	$C_{rss}$		-	20	-	pF	
Gate Resistance	$R_g$	$V_{GS} = 0V, V_{DS} = 0V, f = 1\text{MHz}$	-	2.0	-	$\Omega$	
<b>Switching Characteristics</b> <sup>(7)</sup>							
Turn-On Delay Time	$t_{d(on)}$	$V_{GS} = 10V, V_{DS} = 50V$ $I_D = 20A, R_{GEN} = 3.0\Omega$	-	11.1	-	ns	
Rise Time	$t_r$		-	23	-	ns	
Turn-Off Delay Time	$t_{d(off)}$		-	44	-	ns	
Fall Time	$t_f$		-	32	-	ns	
<b>Gate Charge Characteristics</b> <sup>(7)</sup>							
Total Gate Charge ( $V_{GS} = 10V$ )	$Q_g$	$V_{DS} = 50V, I_D = 20A$ $V_{GS} = 10V$	-	63	-	nC	
Total Gate Charge ( $V_{GS} = 6.0V$ )	$Q_g$		-	40	-	nC	
Gate-Source Charge	$Q_{gs}$		-	16.9	-	nC	
Gate-Drain Charge	$Q_{gd}$		-	11.5	-	nC	
Gate Plateau Voltage	$V_{plateau}$		-	4.1	-	V	
<b>Drain-Source Diode Characteristics</b> <sup>(7)</sup>							
Body Diode Reverse Recovery Time	$t_{rr}$	$I_F = 20A, di/dt = 100A/\mu s,$ $T_J = 25^\circ\text{C}$	-	76	-	ns	
Body Diode Reverse Recovery Charge	$Q_{rr}$		-	180	-	nC	
Diode Forward Current	$I_S$	$T_C = 25^\circ\text{C}$	-	-	186	A	

**Notes:**

1. This current is chip limited, which is calculated based on  $R_{thjc}$ .
2. This current is calculated on single pulse with 10 $\mu s$  Pulse & Duty Cycle = 1%.
3. Defined by design, not subject to production test,  $E_{AS}$  condition:  $T_J = 25^\circ\text{C}, V_{DS} = 50V, V_{GS} = 10V, L = 1.0\text{mH}$ .
4. Device mounted on FR-4 substrate PC board with 2oz copper in 1inch square cooling area.
5. Thermal resistance from junction to soldering point (on the exposed drain pad).
6. Short duration pulse test used to minimize self-heating effect.
7. Defined by design, not subject to production.

Typical Electrical and Thermal Characteristics




Figure 1: Output Characteristics




Figure 2: Transfer Characteristics




Figure 3: On-Resistance vs. Gate-Source Voltage




Figure 4: On-Resistance vs. Drain Current




Figure 5: On-Resistance vs. Junction Temperature




Figure 6: Source-Drain Diode Forward Voltage

Typical Electrical and Thermal Characteristics




Figure 7: Gate Threshold Variation vs. Junction Temperature




Figure 8: Gate Charge Characteristics




Figure 9: Capacitance Characteristics




Figure 10: Power Derating




Figure 11: Current Derating




Figure 12: Safe Operating Area

Typical Electrical and Thermal Characteristics





Figure 13: Normalized Maximum Transient Thermal Impedance

TO220-3L Package Outline

Package Outline







NOTES:

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-1994.
2. ALL DIMENSIONS IN MILLIMETER (ANGLE IN DEGREE).
3. DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH.

DIM.	MILLIMETER		
	MIN.	NOM.	MAX.
A	4.35	4.50	4.70
A1	2.20	2.30	3.00
b	0.70	0.80	0.95
b1	1.10	1.30	1.50
C	0.45	0.50	0.60
C1	1.23	1.30	1.40
H	28.00	28.80	29.80
D	8.80	9.21	9.90
D1	12.80	13.20	13.60
E	9.70	10.00	10.50
E1	7.40	8.00	8.60
L	--	--	3.80
L1	6.25	6.50	6.90
L2	2.40	2.90	3.05
e	2.54 BSC		

**TO263-3L Package Outline**

**Package Outline**



- NOTES:
1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-1994.
  2. ALL DIMENSIONS IN MILLIMETER (ANGLE IN DEGREE).
  3. DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH.

DIM.	MILLIMETER		
	MIN.	NOM.	MAX.
A	4.20	4.50	4.70
A1	2.30	--	2.85
A2	0.00	0.10	0.25
b	0.70	0.80	0.95
b1	1.15	1.30	1.70
C	0.30	0.50	0.60
C1	1.15	1.30	1.42
H	14.00	15.20	15.88
D	8.50	9.20	9.60
D1	6.80	7.75	8.00
E	9.78	10.00	10.36
E1	6.80	7.95	8.10
L	1.50	--	2.80
L1	--	--	1.75
L2	1.35 REF		
e	--	2.54	--

**Recommended Soldering Footprint :**

