



RoHS

REV	ECN NO.	DESCRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	更换图框			2024.04.17

Product Characteristics
Blocks and Clips for Blade Fuses
Compatible Fuses :Automotive Blade Fuses
Electrical Specifications
Rated Voltage: 500 V
Rated Current: From 15 to 30 A
Molded Parts
Insulation Block:
Black Thermoplastic PET (UL94 V-0)
and PA66 (UL94 V-0)
Metal Parts PCB Terminals: Tin Plated Cu Alloy
Electrical
Insulation Resistance:
10,000 Megaohm Minimum at 500 VDC
Contact Resistance: $\leq 5\text{ m}\Omega$ Maximum
Ambient Temperature: $-40\text{ }^{\circ}\text{C}$ to $125\text{ }^{\circ}\text{C}$



3D REFER TO



适用线路板 (PCB LAYOUT)

X.±0.50	X.°±	PART NO: XF-507P-52		XFCN 兴飞连接器	
.X±0.25	.X°±				
.XX±0.15	.XX°±	TITLE: 中号5.2连体插片保险丝座		0769-82001899	
.XXX±0.10	.XXX°±			www.xfconn.com	
UNITS:	mm			DWG NO: /	
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN		APPD		VIEW	
		CHKD		SCALE	SHEET
		DRAW	Wang		REV
		DATE	2024.04.25	NONE	NO A1