








RECOMMENDED PCB PATTERN DIM.

TOLERANCE : ±0.05

Electrical

Voltage:50 V AC(rms)/DC

Current:0.5A AC(rms)/DC

Contact Resistance:40 mΩmax(initial)

Dielectric Withstanding Voltage:200 V AC/rms

Insulation Resistance:500 MΩ min

Operating Temp:-25℃+85℃

MATERIAL:

HOUSING:LCP NATURE(UL94V-0)

TERMINAL:PHOSPHOR BRONZE C5191R-H

P 数	尺 寸				P 数	尺 寸			
	A	B	C	D		A	B	C	D
10	5.50	3.40	2.00	4.96	50	15.50	13.40	12.00	14.96
12	6.00	3.90	2.50	5.46	52	16.00	13.90	12.50	15.46
14	6.50	4.40	3.00	5.96	54	16.50	14.40	13.00	15.96
16	7.00	4.90	3.50	6.46	56	17.00	14.90	13.50	16.46
18	7.50	5.40	4.00	6.96	58	17.50	15.40	14.00	16.96
20	8.00	5.90	4.50	7.46	60	18.00	15.90	14.50	17.46
22	8.50	6.40	5.00	7.96	62	18.50	16.40	15.00	17.96
24	9.00	6.90	5.50	8.46	64	19.00	16.90	15.50	18.46
26	9.50	7.40	6.00	8.96	66	19.50	17.40	16.00	18.96
28	10.00	7.90	6.50	9.46	68	20.00	17.90	16.50	19.46
30	10.50	8.40	7.00	9.96	70	20.50	18.40	17.00	19.96
32	11.00	8.90	7.50	10.46	72	21.00	18.90	17.50	20.46
34	11.50	9.40	8.00	10.96	74	21.50	19.40	18.00	20.96
36	12.00	9.90	8.50	11.46	76	22.00	19.90	18.50	21.46
38	12.50	10.40	9.00	11.96	78	22.50	20.40	19.00	21.96
40	13.00	10.90	9.50	12.46	80	23.00	20.90	19.50	22.46
42	13.50	11.40	10.00	12.96					
44	14.00	11.90	10.50	13.46					
46	14.50	12.40	11.00	13.96					
48	15.00	12.90	11.50	14.46					

					ANGLAR	±5°
ΔX					L≤ 4	±0.2
ΔX					4<L≤ 16	±0.3
ΔX					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5

REVISIONS

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn

UNSPECIFIED TOLERANCES

XKLB

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE:
DWN		VIEW:	PART NO.:
CHKD		UNIT: mm/in	X0511WVS-XXAS-LPV01
APPD		SIZE: A4	DWG NO.:
			WEIGHT
			SHEET
			REVISION
			1/1
			A0