








Engineer Drawing



3D VIEW

NOTES:

- 1.HUOSING: LCP HIGH-TEMP THERMOPLASTIC UL94V-0 COLOR:BEIGE
- 2.TERMINAL:PHOSPHOR BRONZE



RECOMMENDED P.C.BOARD LAYOUT

IPCB 08 471 M XX X X X

① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- ①Series Type
- ②Pitch:0.8mm
- ③Height
- ④Connector Type
- ⑤Pin Code:See Table 1
- ⑥Rows Code
- ⑦Serial Code
- ⑧Other Code

Table 1

Pin Code	NO.of contacts	Dimensions					
		A	B	C	D	E	F
40	40	21.80	15.20	16.80	20.20	18.86	20.21
50	50	25.80	19.20	20.80	24.20	22.86	24.21
60	60	29.80	23.20	24.80	28.20	26.86	28.21
80	80	37.80	31.20	32.80	36.20	34.86	36.21
A0	100	45.80	39.20	40.80	44.20	42.86	44.21
C0	120	53.80	47.20	48.80	52.20	50.86	52.21
E0	140	61.80	55.20	46.80	60.20	58.86	60.21
G0	160	69.80	63.20	64.80	68.20	66.86	68.21
I0	180	77.80	71.20	72.80	76.20	74.86	76.21
K0	200	85.80	79.20	80.80	84.20	82.86	84.21

TOLERANCES:

X.=±0.25

X.X=±0.20

X.XX=±0.10

GENERAL ANGLE

X°=±1°

NCP

www.i-ncp.com

PART NO:
IPCB08471M xxS7V

DRAWING NO
IPCB08471M07V

SHEET 1 OF 1

NAME:
0.8PH H4.7 BTB Male
Receptacle Assembly H5.0

UNITS:mm SCALE:1:1 REV.02