

2.5-6.0V V_{DD} High Sensitivity Omni-Polar Hall Effect Switch

1. Description

MH253EUA Hall-effect sensor is a temperature stable, stress resistant switch. Superior high temperature performance is made possible through a dynamic offset cancellation that utilizes chopper stabilization. This method reduces the offset voltage normally caused by device over molding, temperature dependencies, and thermal stress.

MH253EUA includes the following on a single silicon chip: voltage regulator, Hall voltage generator, small signal amplifier, chopper stabilization, Schmitt trigger, open drain output and push pull output driver, Advanced CMOS wafer fabrication processing is used to take advantage of low voltage requirements, component matching, very low input offset errors, and small component geometries.

MH253EUA is rated for operation between the ambient temperatures 40°C and +85°C for the E temperature range.

2. Features

- CMOS Hall IC Technology
 - Solid State Reliability much better than reed switch
 - Omni polar output switches
 - High Sensitivity for reed switch replacement
 - 100% tested at 125°C for K.
 - Small Size
 - ESD HBM ± 4 KV Min
 - COST competitive
 - RoHS compliant 2011/65/EU and Halogen Free.
-

3. Applications


- Solid state switch
 - Lid close sensor for power supply devices
 - Magnet proximity sensor for reed switch replacement in high duty cycle applications.
 - Safety Key on sporting equipment
 - Revolution counter
 - Speed sensor
 - Position Sensor
 - Rotation Sensor
 - Safety Key
-

4. Ordering Information

Part Number	Temperature Suffix	Package Type B _{RP} (Typ.)
MH253EUA	E (40°C to + 85°C)	(TO-92S)

Table-1 Ordering information

5. Functional Diagram



Note: Static sensitive device; please observe ESD precautions. Reverse VDD protection is not included. For reverse voltage protection, a 100Ω resistor in series with VDD is recommended.

6. Specification

6.1 Absolute Maximum rating

At ($T_a=25^{\circ}\text{C}$)

Parameters	Symbol	Values	Unit
Supply voltage	V_{DD}	7.0	V
Output voltage	V_{OUT}	6.0	V
Reverse voltage	$V_{DD} V_{OUT}$	-0.3	V
Magnetic flux density		Unlimited	Gauss
Output current	I_{OUT}	25	mA
Operating Temperature Range	T_a	-40 to +85	$^{\circ}\text{C}$
Storage temperature range	T_s	-55 to +150	$^{\circ}\text{C}$
Thermal Resistance	θ_{JA}	206	$^{\circ}\text{C}/\text{W}$
	θ_{JC}	148	$^{\circ}\text{C}/\text{W}$
Maximum junction temperature	T_J	150	$^{\circ}\text{C}$
Package Power Dissipation	P_D	606	mW

Table-3 Absolute Maximum rating

Note: Exceeding the absolute maximum ratings may cause permanent damage. Exposure to absolute maximum rated conditions for extended periods may affect device reliability.

6.2. Electric Characteristics


DC Operating Parameters TA=+25°C, VDD=5.0V

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Units
Operating voltage	V _{DD}	Operating	2.5	--	6.0	V
Output Low Voltage	V _{DSON}	I _{OUT} =10mA		--	400	mV
Operating supply current	I _{DD}	Average	--	2.6	6.0	mA
Output Leakage Current	I _{off}	I _{OFF} B<BRP, V _{OUT} = 5V	--		10	uA
Electro Static Discharge	HBM		4	--		KV
Hysteresis	B _{HYS}	BOP _x -BRP _x	--	10	--	Gauss
Output rise time	t _r	R _L =10kΩ, C _L =20pF	--		0.45	uS
Output fall time	t _f	R _L =10kΩ, C _L =20pF	--		0.45	uS
Release Point	B _{RPS}	S pole to branded side, B < BRP, V _{out} Off	5.0	20		Gauss
	B _{RPN}	N pole to branded side, B < BRP, V _{out} Off		-20	-5	
Operate Point	B _{OPS}	S pole to branded side, B > BOP, V _{out} On		30	60	Gauss
	B _{OPN}	N pole to branded side, B > BOP, V _{out} On	-60	-30		


Table-4 Electric Characteristics

7. Typical Application circuit


Open Drain



Push Pull



8. Dimension (TO-92S)



Dimension; mm

Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	1.420	1.620	0.056	0.064
A1	0.660	0.860	0.026	0.034
b	0.350	0.480	0.014	0.019
b1	0.400	0.550	0.016	0.022
c	0.360	0.510	0.014	0.020
D	3.900	4.100	0.154	0.161
D1	2.280	2.680	0.090	0.106
E	3.050	3.250	0.120	0.128
e	1.270 TYP.		0.050 TYP.	
e1	2.440	2.640	0.096	0.104
L	15.100	15.500	0.594	0.610
θ	45°TYP.		45°TYP	

DISCLAIMER

ELECSUPER PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with ElecSuper products. You are solely responsible for

- (1) selecting the appropriate ElecSuper products for your application;
- (2) designing, validating and testing your application;
- (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements.

These resources are subject to change without notice. ElecSuper grants you permission to use these resources only for development of an application that uses the ElecSuper products described in the resource. Other reproduction and display of these resources are prohibited. No license is granted to any other ElecSuper intellectual property right or to any third party intellectual property right. ElecSuper disclaims responsibility for, and you will fully indemnify ElecSuper and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources. ElecSuper's products are provided subject to ElecSuper's Terms of Sale or other applicable terms available either on www.elecsuper.com or provided in conjunction with such ElecSuper products. ElecSuper's provision of these resources does not expand or otherwise alter ElecSuper's applicable warranties or warranty disclaimers for ElecSuper products.