



REV.	DESCRIPTION	ECN NO.	NAME	DATE

PRELIMINARY
DESIGN IS SUBJECT
TO CHANGE WITHOUT
PRIOR NOTICE

- 技术要求:
- 1、塑件材料:PA66
 - 2、接触件:黄铜镀锡
 - 3、接触电阻: $\leq 10m\Omega$
 - 4、绝缘电阻: $\geq 1000M\Omega$
 - 5、额定电压:250V AC DC
 - 6、额定电流:2.0A AC DC
 - 7、耐压:能承受1000V AC/Min ute
 - 8、工作温度: $-25^{\circ}\sim\sim+85^{\circ}$
 - 9、可焊性试验:浸锡面积 $\geq 95\%$ 温度 220^{+5}_{-0} ,时间 2.5 ± 0.5 秒
 - 10、铅和镉等六大有害物质含量要符合环保要求

Part No	PIN	A	B	C
WF-1B200B2P	2	2	6	
WF-1B200B3P	3	4	8	2
WF-1B200B4P	4	6	10	4
WF-1B200B5P	5	8	12	6
WF-1B200B6P	6	10	14	8
WF-1B200B7P	7	12	16	10
WF-1B200B8P	8	14	18	12
WF-1B200B9P	9	16	20	14
WF-1B200B10P	10	18	22	16
WF-1B200B11P	11	20	24	18
WF-1B200B12P	12	22	26	20
WF-1B200B13P	13	24	28	22
WF-1B200B14P	14	26	30	24
WF-1B200B15P	15	28	32	26

2	Contact	Brass	n*1	电镀(锡): 整个表面镀底镍30u"MIN,再镀锡80u".MIN.
1	Wafer	PA66(UL94V-0)	1	本色
序号	名称	材料	数量	附注

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD			
DIM.	TOL.	TITLE: WAFER 2.0mm H8.0mm 90° DIP			
X		DWG. NO.: WF-1B200BNP		DRAWN: MAX	
X.X	± 0.30	PART NO.: WF-1B200BNP		CHECKED: ELLA	
X.XX	± 0.25	UNIT: mm		APPROVED: WILL	
X.XXX	± 0.15	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn
GENERAL	ANGLE: $\pm 3^{\circ}$				

BXCONN[®]

