






EEF432130C-171M-D

PARAMETER	SPECIFICATION	CONDITION	TEST INSTRUMENTS
L(uH)	170± 20%	40KHz/0.1V	MICROTEST 6377
DCR(mΩ)	15MAX	At 25℃	TH2512A
I sat(A)	35A TYP L0A*70%	40KHz/0.1V	MICROTEST 6377+6220
I rms(A)	35A TYP ΔT=40℃	40KHz/0.1V	MICROTEST 6377+6220

ITEM	MATERIAL	SUPPLIER
CORE	EEF4321C-60u	SHANGPENG/DONGYANGGUANG/TIANTONG
WIRE	(1.0*6.0*20TS)	TAIYI-JIATENG-SONGYE
SOLDER	TIN-Sn99.95	QIANDAO/HONGXINGWEI



COILMX

25