



REV.	DESCRIPTION	ECN NO.	NAME	DATE

Part No	Pin	A	B	C
WF-1D100A2P	2	1.00	5.00	2.40
WF-1D100A3P	3	2.00	6.00	3.40
WF-1D100A4P	4	3.00	7.00	4.40
WF-1D100A5P	5	4.00	8.00	5.40
WF-1D100A6P	6	5.00	9.00	6.40
WF-1D100A7P	7	6.00	10.00	7.40
WF-1D100A8P	8	7.00	11.00	8.40
WF-1D100A9P	9	8.00	12.00	9.40
WF-1D100A10P	10	9.00	13.00	10.40
WF-1D100A11P	11	10.00	14.00	11.40
WF-1D100A12P	12	11.00	15.00	12.40
WF-1D100A13P	13	12.00	16.00	13.40
WF-1D100A14P	14	13.00	17.00	14.40
WF-1D100A15P	15	14.00	18.00	15.40
WF-1D100A16P	16	15.00	19.00	16.40
WF-1D100A17P	17	16.00	20.00	17.40
WF-1D100A18P	18	17.00	21.00	18.40
WF-1D100A19P	19	18.00	22.00	19.40
WF-1D100A20P	20	19.00	23.00	20.40

技术要求Specification:

- 1、材质Material: PA66 UL94V-0;
- 2、塑件表面平整光洁, 无明显的毛刺、气泡、变形、浇口拉伤、缺料等不良现象。
Plastic surface smooth and clean, no obvious burrs, bubbles, distortion, gate strain, lack of material and other undesirable phenomena.

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD			
DIM.	TOL.	TITLE: SH1.0MM HOUSING			
X		DWG. NO.: WF-1D100ANP		DRAWN: MAX	
X.X	±0.30	PART NO.: WF-1D100ANP		CHECKED: ELLA	
X.XX	±0.25	UNIT: mm		SCALE: none	APPROVED: WILL
X.XXX	±0.15	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn	
GENERAL ANGLE: ±3°					

