



REV.	DESCRIPTION	ECN NO.	NAME	DATE

Part No	Pin	A	B
WF-1B254B2P	2	2.50	7.50
WF-1B254B3P	3	5.00	10.00
WF-1B254B4P	4	7.50	12.50
WF-1B254B5P	5	10.00	15.00
WF-1B254B6P	6	12.50	17.50
WF-1B254B7P	7	15.00	20.00
WF-1B254B8P	8	17.50	22.50
WF-1B254B9P	9	20.00	25.00
WF-1B254B10P	10	22.50	27.50
WF-1B254B11P	11	25.00	30.00
WF-1B254B12P	12	27.50	32.50
WF-1B254B13P	13	30.00	35.00
WF-1B254B14P	14	32.50	37.50
WF-1B254B15P	15	35.00	40.00
WF-1B254B16P	16	37.50	42.50
WF-1B254B17P	17	40.00	45.00
WF-1B254B18P	18	42.50	47.50
WF-1B254B19P	19	45.00	50.00
WF-1B254B20P	20	47.50	52.50

技术要求:

1. 塑件材料: PA66(UL-94V-0)
2. 接触件: 黄铜镀锡
3. 接触电阻:  $\leq 10m\Omega$
4. 绝缘电阻:  $\geq 100M\Omega$
5. 额定电压: 250V AC DC
6. 额定电流: 2.0A AC DC
7. 耐压: 能承受 1000V AC/Minute
8. 工作温度:  $-25^{\circ} \sim +85^{\circ}$
9. 可焊性试验: 浸锡面积  $\geq 95\%$  温度  $235^{\circ}$ , 时间  $2.5 \pm 0.5$  秒
10. 铅和镉等六大有害物质含量要符合环保要求。

SUGGESTED PCB LAYOUT  
(COMPONENT SIDE)

2	Contact	Brass	n*1	电镀(锡): 整个表面镀底锡30u"MIN, 再镀锡80u"MIN.
1	Wafer	PA66(UL94V-0)	1	白色
序号	名称	材料	数量	备注
GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD		
DIM. TOL.		TITLE: WAFER XHB2.54MM 带扣 弯脚		
X				
X.X	$\pm 0.30$			
X.XX	$\pm 0.25$			
X.XXX	$\pm 0.15$			
GENERAL ANGLE:		DWG. NO.: WF-1B254BNP		
$\pm 3^{\circ}$		DRAWN: MAX		
		PART NO.: WF-1B254BNP		
		CHECKED: ELLA		
		APPROVED: WILL		
UNIT: mm		SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4
		LAYER: bxconn		

BXCONN<sup>®</sup>

