



Part Number : 1205000246

Series Number : 120500

Product Category : Circular Industrial Cordsets

Product Description : Micro-Change (M12) Single-Ended Cordset, 4 Poles, L-Coded, Male (Straight) to Pigtail, 14 AWG, Black TPU WSOR Cable, 10.0m (32.81') Length

Status : Active

Engineering Number : L0P4006B65M100

Documents & Resources

Drawings

Drawing 1205000246_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant with Exemption 10(a); 3 per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120500
Description	Micro-Change (M12) Single-Ended Cordset, 4 Poles, L-Coded, Male (Straight) to Pigtail, 14 AWG, Black TPU WSOR Cable, 10.0m (32.81') Length
IP Rating	IP67
Product Family	Brad Micro-Change (M12) Connectors
Product Name	Micro-Change (M12)
Region	Asia, Europe
Type	Single Ended
UPC	193264519729

Agency

UL	E152210
----	---------

Electrical

Current - Maximum per Contact	12.0A
Voltage - Maximum	63V

Physical

Cable Diameter	10.10mm (.397")
Cable Length	10.0m (32.81')
Color - Cable Jacket	Black
Connector End A	Micro-Change (M12)
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Male-Pigtail
Keyway	L-Coded
LED Indicator	No
Material - Cable Jacket	WSOR TPU

Material - Connector Body	TPE
Material - Contact	Brass
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	1713.110/g
Orientation	Straight to Pigtail
Poles	4
Temperature Range - Operating	-25° to +85°C
Wire/Cable Type	UL 21215
Wire Size (AWG)	14

This document was generated on Apr 12, 2024