



A		B		C		D		E	
REV.	DESCRIPTION				ECN NO.	NAME	DATE		






技术要求:


1. 塑料材料: PA66 (UL-94V-0)
2. 接触件: 黄铜镀锡
3. 接触电阻: $<10m\Omega$
4. 绝缘电阻: $\geq 1000M\Omega$
5. 额定电压: 250V AC DC
6. 额定电流: 3.0A AC DC
7. 耐压: 能承受 1000V AC/Minute
8. 工作温度: $-25^{\circ}\sim +85^{\circ}$
9. 可焊性试验: 浸锡面积 $>95\%$ 温度 $235^{\pm 5}_{0}$, 时间 2.5 ± 0.5 秒
10. 铅和铜等六大有害物质含量要符合环保要求

PRELIMINARY
DESIGN IS SUBJECT
TO CHANGE WITHOUT
PRIOR NOTICE

Part No	PIN	A	B
WF-1B254A2P-R	2	2.5	7.5
WF-1B254A3P-R	3	5.0	10.0
WF-1B254A4P-R	4	7.5	12.5
WF-1B254A5P-R	5	10.0	15.0
WF-1B254A6P-R	6	12.5	17.5
WF-1B254A7P-R	7	15.0	20.0
WF-1B254A8P-R	8	17.5	22.5
WF-1B254A8P-R	9	20.0	25.0
WF-1B254A9P-R	10	22.5	27.5
WF-1B254A11P-R	11	25.0	30.0
WF-1B254A12P-R	12	27.5	32.5
WF-1B254A13P-R	13	30.0	35.0
.....
WF-1B254A20P-R	20	$(20-1)*2.5$	$(20+1)*2.5$



SECTION A-A



SUGGESTED PCB LAYOUT
(COMPONENT SIDE)

2	Contact	Brass	n*1	电镀(锡): 整个表面镀成镍30u"MIN, 再镀锡80u"MIN.
1	Wafer	PA66(UL94V-0)	1	红色
序号	名称	材料	数量	附注
GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD		
DIM. X X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 GENERAL ANGLE: ±3°		TITLE: WAFER 2.54mm H7.0mm 90° DIP 红色		
DWG. NO.: WF-1B254ANP-R		DRAWN: MAX		
PART NO.: WF-1B254ANP-R		CHECKED: ELLA		
UNIT: mm	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn
APPROVED: WILL				

BXCONN[®]

