

RoHS

SPECIFICATIONS

Rated Current:1.5AMP

Contact Resistance:20mΩ Max

Withstand Voltage:500V AC/DC

Insulation Resistance:1000MΩ Min

Operation Temperature:-40℃ to +105℃

Contact Material:Brass





Contact Plating:Au Over Ni

Insulator Material:Polyester(UL94V-0)

Standard: PA6T

Max.Processing Temp: 230℃ for 30-60 seconds
(260℃ for 5 seconds)

Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



Dimension antitheses list

ITEM	PC	PA	L
Standard	2.80	3.90	8.70
Alternate			

OPERATION

DRAW

SCALE

FIT

深圳市连盛精密连接器有限公司

X.X ±0.30

DRAW

UNIT

mm

X.XX ±0.20

CHECK

SIZE

A4

X.XXX ±0.10

CHECK

SHEET

1/1

Angle ±3°

APPROVE

PROJ.

◆

PART NO.

1010200277

TITLE:

2.0PH 2x17pin H2.0mm DIP PA3.9
PC2.8

A0 2012.04.11 NEW DRAWING

REV DATE MODIFICATION DESCRIPTION

CHANGE

DIM

TOL

APPROVE

PROJ.

◆

PART NO.

1010200277

TITLE:

2.0PH 2x17pin H2.0mm DIP PA3.9
PC2.8