



NO.	PART NAME	MATERIAL	QTY	FINISHING
11	大直针	H62黄铜带 Y=0.6mm	1	D. Cu/Sn
10	右长针	H62黄铜带 Y=0.6mm	1	D. Cu/Sn
9	左长针	H62黄铜带 Y=0.6mm	1	D. Cu/Sn
8	右中针	H62黄铜带 Y=0.6mm	1	D. Cu/Sn
7	左中针	H62黄铜带 Y=0.6mm	1	D. Cu/Sn
6	左短针	H62黄铜带 Y=0.6mm	1	D. Cu/Sn
5	小直针	H62黄铜带 Y=0.6mm	1	D. Cu/Sn
4	右短针	H62黄铜带 Y=0.6mm	1	D. Cu/Sn
3	接地针	H62黄铜带 Y=0.25mm	1	D. Cu/Sn
2	后盖	PBT	1	黑色
1	底座	PBT	1	黑色

TOLERANCE UNLESS SPECIFIED									
UP TO 5mm: ±0.1	ANGULAR	A1	2018.4.13	更新图面					
ABOVE 5mm: ±0.2	±1°	NO	DATE	REVISIONS		BY	APPD		
TITLE: DIN JACK				UNIT : MM	ROHS COMPLIANT	DWN			
MODEL: DIN-804				SCALE: 1:1		CHK'D			
东莞市六钧电子五金有限公司						APPD			
						PRO.AGL:			REV :A1