





RoHS

SPECIFICATIONS

Rated Current:1.5AMP
 Contact Resistance:20mΩ Max
 Withstand Voltage:500V AC/DC
 Insulation Resistance:1000MΩ Min
 Operation Temperature:-40°C to +105°C

Contact Material:Brass
 Contact Plating:Au or Sn Over Ni
 Insulator Material:Polyester(UL94V-0)
 Standard: PA6T
 Max.Processing Temp: 230°C for 30-60 seconds
 (260°C for 5 seconds)

Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE±0.05)



Ordering Information

P 2 C 2 14 1 5 00 4 2208
 产品类型 P=排针
 间距 2=2.0
 塑胶高度 C=2.0
 排数 2=双排
 单排PIN数 2~40P
 产品形态 1=DIP
 塑胶材料 2=LCP
 5=PA6T
 电镀厚度 00=带漆
 01=AU1U
 包装方式 1=管装
 2=卷装
 3=盘装
 4=袋装
 5=盒装
 序列号

Dimension antitheses list							
ITEM	PA	PB	PW	PC	L	H	W
001	3.9			2.8	8.7	2.0	4.0
Alternate							

				OPERATION		DRAW		SCALE		FIT		深圳市连盛精密连接器有限公司 PART NO. 1010200675 TITLE: 2.0PH H=2.0 2*14P DIP PA3.9 PC2.8 L=8.7 AU0.6U PA6T	
				X.X	±0.30			UNIT	mm				
				X.XX	±0.20	CHECK		SIZE	A4				
				X.XXX	±0.10	APPROVE		SHEET	1/1				
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	DIM	TOL			PROJ.	◆				
A0	2012.04.11	NEW DRAWING											