

RoHS

SPECIFICATIONS

Rated Current:1.5AMP

Contact Resistance:20mΩ Max

Withstand Voltage:500V AC/DC

Insulation Resistance:1000MΩ Min

Operation Temperature:−40℃ to +105℃

Contact Material:Brass





Contact Plating:Au or Sn Over Ni

Insulator Material:Polyester(UL94V−0)

Standard: PA6T

Max.Processing Temp: 230℃ for 30−60 seconds
(260℃ for 5 seconds)

Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



Ordering Information

P 2 C 1 07 1 5 00 4 2195

产品类型
P=排针

间距
2=2.0

塑胶高度
C=2.0

排数
1=单排

单排PIN数
1~40P

产品形态
1=DIP

塑胶材料
5=PA6T

电镀厚度
00=常规
01=1u"
02=2u"
03=3u"

包装方式
1=管装
2=卷装
3=盘装
4=袋装
5=盒装

序列号

Dimension antitheses list							
ITEM	PA	PB	PW	PC	L	H	W
001	3.9			2.80	8.7	2.0	2.0
Alternate							

				OPERATION		DRAW			SCALE	FIT	深圳市连盛精密连接器有限公司	
				X.X	±0.30					UNIT		
				X.XX	±0.20	CHECK			SIZE	A4		
A0	2012.04.11	NEW DRAWING		X.XXX	±0.10					SHEET	1/1	PART NO.
				Angle	±3°	APPROVE					TITLE:	2.0PH H=2.0 1*7P DIP PA3.9 PC2.8 L=8.7 AU0.6U PA6T
REV	DATE	MODIFICATION DESCRIPTION		CHANGE	DIM		TOL			PROJ.		