



REV.	DESCRIPTION	ECN NO.	NAME	DATE

PRELIMINARY
DESIGN IS SUBJECT
TO CHANGE WITHOUT
PRIOR NOTICE

- 技术要求:
1. 塑件材料: PA66
 2. 接触件: 黄铜镀锡
 3. 接触电阻: $\leq 10m\Omega$
 4. 绝缘电阻: $\geq 1000M\Omega$
 5. 额定电压: 250V AC DC
 6. 额定电流: 2.0A AC DC
 7. 耐压: 能承受 1000V AC/Minute
 8. 工作温度: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$
 9. 可焊性试验: 浸锡面积 $\geq 95\%$ 温度 $220 \pm 5^{\circ}\text{C}$, 时间 2.5 ± 0.5 秒
 10. 铅和铜等六大有害物质含量要符合环保要求

Part No	PIN	A	B	C
WF-1A200B2P	2	2	6	
WF-1A200B3P	3	4	8	2
WF-1A200B4P	4	6	10	4
WF-1A200B5P	5	8	12	6
WF-1A200B6P	6	10	14	8
WF-1A200B7P	7	12	16	10
WF-1A200B8P	8	14	18	12
WF-1A200B9P	9	16	20	14
WF-1A200B10P	10	18	22	16
WF-1A200B11P	11	20	24	18
WF-1A200B12P	12	22	26	20
WF-1A200B13P	13	24	28	22
WF-1A200B14P	14	26	30	24
WF-1A200B15P	15	28	32	26

2	Contact	Brass	n*1	电镀(锡): 整个表面镀底镍30u"MIN, 再镀锡80u".MIN.
1	Wafer	PA66(UL94V-0)	1	本色
序号	名称	材料	数量	附注

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD		
DIM.	TOL.	TITLE: WAFER 2.0mm H8.0mm 180° DIP		
X		DWG. NO.: WF-1A200BNP		
X.X	± 0.30			
X.XX	± 0.25	PART NO.: WF-1A200BNP		
X.XXX	± 0.15			
GENERAL ANGLE:	$\pm 3^{\circ}$	UNIT: mm	SCALE: none	SHEET: 1 of 1
		DWG. SIZE: A4	LAYER: bxconn	APPROVED: WILL

